



Overview

Model Name	APC Replacement Battery Cartridge #12
Includes	All required connectors
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	Stand alone battery stack
Battery mounting	3 - 5
RBC Quantity	1
Replacement battery cartridge note	RBC 12 is composed of two separate battery cells. The Net dimensions are measured per cell.

Physical

Net Weight	20.0 kg
Maximum Height	97.0 mm
Maximum Width	254.0 mm
Maximum Depth	152.0 mm
Shipping Weight	22.86 kg
Shipping Width	394.0 mm
Shipping Height	229.0 mm
Shipping Depth	572.0 mm
Color	Black
Units per Pallet	20.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %

Storage Elevation	0-15000 meters
-------------------	----------------

Conformance

Standard warranty	1 year repair or replace
-------------------	--------------------------

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
