
2" J-HOOK WIDE/RET - 90° ANGLE CLIP 3/8" ROD

CJ32HAC6 | [Cablofil](#)



FEATURES & BENEFITS

CJH Series J-Hooks are uniquely designed with 49% more cable capacity than our competitors, even when the overall "size" is larger. That means you can hold even more cables. With a wide cable bearing surface that's 32% larger and smooth tapered edges, our J-Hooks provide stress-free support all the way to maximum capacity. Each J-Hook features multiple threaded and pre-drilled holes and is available with various attachment options, speeding up on-site installation no matter where you need them.



- Wide hook base provides 32% more cable bearing surface
- 4 times greater load capacity
- Ready to use out of the box, reducing installation time and labor costs
- Wire cable retainer clip included but not shown
- Multiple threaded and pre-drilled holes for easy mounting
- Smooth, beveled edges provide NEC and TIA Standards compliant bend radius
- Use for all common low voltage cable, fiber optic and coax cable types

SPECIFICATIONS

GENERAL INFO

Color: Pre-Galvanized
Type: J-Hook

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

TECHNICAL INFORMATION

Material: Steel

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

