

iBridge Video Doorbell IBV-DBELL Series

1080P 2MP HD Video Doorbell is the ideal new service for accounts to watch for deliveries, screen guests, look out for potential thieves & more - easy installation for new and existing security systems

Professional grade 1080HD video, two-way audio, customizable motion sensors & top IP65 ingress rating

- ✓ HD Video with two-way talk & noise-cancellation
- ✓ Custom PIR motion zones
- ✓ Day & Night Live-View & archived video with infrared night vision
- Sends instant alerts to accounts when visitors press the doorbell or trigger the built-in motion sensors, so they can hear and speak to anyone at the door from any smartphone, tablet or PC.
 - Motion-activated alerts
 - Video on Demand with Live-View
- Simple 3-button operation Buttons appear on smartphone screen over video Press "Accept" to talk (2-way chat), or "Hang up" to disconnect, or "Mute" to just watch
- Durable & weather-resistant, IP-65 Rated and with operating range from -4 to 122°F
- Slim 4.7" x 1.9" x 1.1" iBridge Video Doorbell fits virtually anywhere
- PIR motion detection has three configurable zones, and a broad 140° angle of view, as well as IR-powered night vision
- Doorbell is easily enrolled and appears like any other WiFi iBridge Video Camera in the full integrated iBridge Connected Home or Standalone iBridge Video ecosystem, uses free Apps on iTunes®/Google Play®
- Time/date-stamped video is also cloud-archived for later review
- 12-mos. cloud-based video storage included
- Uses existing doorbell power & wiring, with quick 2-wire AC installation
- Over the Air (OTA) automatic firmware updates
- Free Consumer Mailers/Statement Stuffers







Cloud-based time stamped video archive (12mos, incld)

On any smartphone, consumers get a text and video that someone's at the door. They simply press "accept" to talk (2-ways), or "hang up" to disconnect or "mute" to just watch. Ideal for watching for deliveries, guest-screening & more.



iBridge Video Doorbell









Accounts can chat with someone at the door from anywhere they are







Specifications: IBV-DBELL Series

	V	Ì	d	e	0

Video Compression H.264 1/2.7" 2MP Image Sensor

(20fps) (1920 x 1080) CMOS

Lens 1.9mm Angle of View Day/Night

H:140° **ICR**

Audio

Audio Compression G.711 Audio Input Omnidirectional Mic Audio Output

Built-in Speaker **Bidirectional Talk** Support Dual-way

Bidirectional talk

Operation Mode

Button Single Mechanical Button Motion Detection PIR, H:120°

Network

WiFi IEEE802.11b/g/n, 2.4GHz Standalone iBridge Video App(s) or iBridge Connected

Home/Biz, on iTunes® or Google Play®

Compliances CE, UL, FCC

General

Ingress Protection

Memory Slot Installation Material

Power

Power Consumption Working Environments Relative Humidity

Dimensions Weight

Ordering IBV-DBELL

A731

A696

IP65 (Dust-tight, complete protection; Protection from water (dripping, spraying, splashing & even water jetted from a nozzle (6.3mm) Micro SD, Max 64GB Surface ABS, Plastic 16-24VAC (optional 12-24DC w/ addl power supply)

Standby<3W, Active <5W -4° to +122°F (-20°C to +50°C)

10%~95%RH 4.69"h×1.85"w×1.14"d

0.66 lb.

WiFi Doorbell, built-in Multidirectional Mic/speaker, 1080P Pro Grade w/ Night Vision, Dark Metallic Gray (standard), AC with full mounting hardware. Includes 12 months cloud storage.

IBV-DBELL-MGS As above, in Silver finish **IBR-TOUCH**

Integrated Touchscreen, Video-View & Security System Control for Napco, Honeywell/ADT® & DSC® Sys Free Enduser iBridge Video Doorbell

Residential Mailers/Stuffers (right) For Full iBridge Video Camera Line, see spec sheet

:140

