

# iBridge<sup>®</sup> Touch

## 7" Color Touchscreen for Security, Video, Smart Home & Business



### EASY TO USE With IoT & Matching App



### VIDEO 6-Camera Viewing



### SMART AUTOMATION Enhanced Z-Wave



### SECURITY ICONS/KEYPADS ADT<sup>®</sup>/Honeywell<sup>®</sup>, DSC<sup>®</sup>, Napco



#### FEATURING:

- All-new intuitive, wall-mounted touchscreen control of security system and/or optional video and smart home or business automation, with Z-Wave<sup>®</sup> locks, lights, temp & small appliances\*
- Brilliant 7-inch high-res color 1024 x 600 TFT capacitive display
- Ultra-responsive, high-speed, quad-core processor
- Choice of hardwired or wireless iBridge Touch<sup>™</sup> models, WiFi models with 12V plug-in transformer (supplied)
- Slimline, clean decor-friendly design and GUI; matches new iBridge App
- Built in voice prompts and sounder speaker
- Easy Icon Security Control &/or Matching Conventional Keypad Control of Napco Gemini and other leading brand panels; also arm/disarm control of any panel with a keyswitch input

#### SECURITY:

- Easy icon one-button control of Arm, Stay, Away etc.
- Also mirrors top brand keypads in conventional keypad mode, supports ADT<sup>®</sup>/Honeywell<sup>®</sup>, DSC<sup>®</sup>, Napco Gemini, etc.
- Can also be used with any brand control panel with keyswitch input for one-button arm/disarm
- Entry/Exit countdown displayed
- Three Emergency buttons
- Quickly and easily bypass zones

#### VIDEO:

- Multiview on-premises viewing of up to 6 cameras, with easy scroll and finger-spread zoom display
- Choice of iBridge Video<sup>™</sup> Cameras (also supports original iSeeVideo Cameras). WAP-free; connectivity via either StarLink Connect<sup>®</sup> or iBR-ZREMOTE Module
- Video can be added as MMS notifications and event/scene triggers
- Easy camera enrollment

#### SMART AUTOMATION / IOT:

- Choice of smart automation IoT integration panel interface – universal StarLink Connect Dual Path Communicator with Built-in Z-Wave Hub (-Z model). For use with any panel with keyswitch, automation scenes on arm/disarm. Or for Napco-only option: or Gemini hardwire or WiFi iBridge Z-Remote Panel Module
- Supports standard Z-Wave Devices for home or biz smart control and increases range performance up to 100%
- Create and control custom scenes, ideal for smart home or business, combining security, video and/or automation-controlled devices by touch, by trigger event or by schedule
- Dealer scene-creation auto-generates custom button for consumer use/ touch-activation



StarLink Connect<sup>®</sup> adds Universal Cell/IP, IoT Control<sup>®</sup>, SMS alerts & Keypad App for Top Brands (also keyswitch or Gemini Z-Remote options for connectivity)

## NOTIFICATIONS:

- **Onscreen notification viewing of SMS text or MMS** multimedia notifications
- **Also easy menu-driven ability for user to set or modify their own notifications by category**, e.g., alarm event, business, family, pet care, elder care, vacation, etc.



## DEALER EASE:

- **Easy Setup Wizard & System Configuration** with at-a-glance Full Account Info Screen



- **Easiest WiFi connection (802.11)** with automatic choose-a-network display & color-coded signal strength optimizer
- Add or delete User Codes
- Selectable Security-Only Mode (doesn't show unavailable options for applications currently without video or automation)
- **Choose your Panel Brand's Conventional Keypad Style & Even Do Keypad-Programming Your Way on Touchscreen:**

Arm/Disarm icons or Mirrors keypad from popular brands, ADT®/Honeywell®, DSC®, Napco



- Easy firmware updates onscreen
- 4 Touchscreens supported per system
- Easy 3-Gang Box wall-mount installation (both models)
- **Eligible product for iBridge Connected Home & Business Authorized Dealer Program**

## SPECIFICATIONS:

### ELECTRICAL RATINGS

- **Speaker:** 1 Integral 2W
- **Screen on, idle:** 300mA
- **Clicking menu items:** 380mA
- **Power:** **IBR-TOUCH-WL**, powered by a supplied 12VDC adapter, wireless WiFi connectivity. (See details Touchscreen WI2296LF & StarLink Connect WI2193A)
- **IBR-TOUCH**, with hardwire security connectivity plus WiFi support for Z-Wave & video. (See details Touchscreen WI2296LF & StarLink Connect WI2193A)
- **Four (4) Touchscreens supported** per security system



## FEATURES:

- **CPU:** Quad core processor, (up to 1.6GHz)
- **Wi-Fi:** 802.11b/g/n with integral antenna
- **LCD Size:** 7 inch digital screen
- **Resolution Ratio:** 1024 x 600 x, 16:9 aspect ratio, 16.7 million colors
- **Pixels:** 1024 x RGB (3) x 600
- **Touch Screen:** Digital and full-screen, capacitive
- **OS:** Android
- **Smart automation/IoT integration panel interface options (where enabled):** universal StarLink Connect Dual Path Communicator with Built-in Z-Wave Hub (-Z model) or Gemini hardware or WiFi iBridge Z-Remote Panel Module
- **Video:** **View up to 6 cameras, choice of new iBridge Video Cameras (No WAP) or iSee Video Cameras\***
- **Easy WiFi Connection:** Choose-a-network display, shows available WiFi networks; color-coded onscreen signal strength optimizer indicates green (good), yellow (trouble) or red (no-go)

## HOUSING:

- **Dimensions (HxWxD):** 5-3/8 x 7-7/8 x 7/8 in. (13.7 x 20 x 2.2 cm)
- **Weight:** 14.3oz (405g)
- **Operating Temperature:** 0-49°C (32-120°F)

## ORDERING INFO:

- **IBR-TOUCH-WL** 1024 x 600 7" hi-res color touchscreen for security and optional automation or video control (using StarLink Connect or IBR-ZREMOTE), wireless connectivity, powered by 12VDC adapter, supplied.
- **IBR-TOUCH** similar to above, but with hardwire security connectivity plus WiFi support for Z-Wave & video (using StarLink Connect or IBR-ZREMOTE.)
- **IBRIDGE APP** New & Improved Matching Smart Device App for remote control, mirroring touchscreen look and operation including security icons and conventional keypad modes (top panels), for easy consumer use. Available on Google Play® or iTunes®

## COMPLEMENTARY OPTIONS:

- **SLE-CDMA-Z For IoT &/or Video Touchscreen support\***, Universal Dual Path Cell/IP Communicator, Verizon Network Certified® CDMA, with Built-in Smart Hub with Z-Wave Control, Virtual Keypad App, SMS/MMS Notification and full keypad bus support of leading panel brands, Honeywell®/ADT®, DSC®, Napco or abridged support of any panel brand with keyswitch input.
- **SLE-LTEV-Z** as above but, Verizon Network Certified® LTE
- **SLE-GSM-3/4G-Z** as above, but on AT&T Network
- **IBR-ZREMOTE** Remote Service/Z-Wave Control Module for Gemini Expandable Panels, significantly expands Z-Wave device range (supports standardly available devices)
- **IBR-ZREMOTE-W** As above, but easy WiFi -connected model
- **ISV2-CAM iBridge Video Camera**, 2-way audio built in mic/speaker and 32GB onboard video storage (up to 7 days HD video 720p). Professional grade, fast-connect, up to 20/30 fps 2.4GHz WiFi 802.11 b/g/n, 1.3MP (1280x960) CMOS High Def. Sensor.
- **ISV2-PT iBridge Video Pan/Tilt Camera**, WiFi Hi-Def. P/T Camera, true 2-way audio built in mic/speaker and 32GB onboard video storage (up to 7 days HD video 720p).
- **ISV2-DOME iBridge Video Outdoor Dome Camera**, Outdoor Dome Camera, WiFi Hi-Def. Indoor/Outdoor Dome Camera with POE option and 32GB onboard video storage (up to 7 days HD video 720p). Ingress & Vandal- Protected Weatherproof camera (IP67, IK10).
- **iBridge Touch Touchscreen Instruction Manual** WI2296LF
- **StarLink Connect Instruction Manual** WI2193A