



SALAMANDER
DESIGNS

UNIFI HUDDLE™



UNIFI HUDDLE™

The Salamander Designs Unifi Huddle™ Tables provide the latest in high-quality, customizable solutions so teams can gather quickly and collaborate more easily. Unifi Huddles consist of two models that provide the latest in table solutions to accommodate today's modern offices and impromptu meetings.

Both designs are easy to specify for rapid deployment and offer innovative solutions to support and manage today's technology. Ultra simple to install in just minutes, Unifi is built to last and a future-proof design allows technology updates easily.



UNIFI HUDDLE™

Ideal for 2 to 5 people seated, Unifi offers select mounting solutions to support virtually any unified communication technology. A premium-grade cabinet features storage for larger AV systems with quick access and easy cable management. Other thoughtful options include power distribution and cooling systems.



UNIFI HUDDLE™ LITE

Since one size doesn't fit all, the smaller Unifi Huddle Lite accommodates 2 to 3 people at cafe-height and is ideal for a fast-paced environment where people gather often in an impromptu manner. The Unifi Lite is available with or without integrated display mount and features a unique under table storage base is easily accessible for small AV systems.

Four table top options.




UNIFI HUDDLE™ LITE

2-3 PERSON, 39" CAFE-HEIGHT

UNIFI HUDDLE™

2-5 PERSON SEATED



Boat Shape Table

Optimized to provide ideal camera field of view



Low Impact Installation

Easy to deploy, simple to move



Aluminum Chassis Cabinet

Includes 3RU vertical rack and adjustable tray shelves



Wire Management

Throughout open cabinet, back with fully open interior and raceway up to display and to table

Customize Your Unifi Huddle™

with optional mounts, cut-ins and interior accessories for a complete turnkey video conference solution.



VIDEO CONFERENCE



A. Universal Single or *Dual Display Mounts with Adjustable Positions

** 338 Cabinet Model Only*



B. Speaker/Camera Mount

Speaker sold separately



C. Tech Shelf

Camera sold separately



CONNECTION PORTS

Ports can be placed in various locations throughout table and cabinet. Reference page 7 for location specs.



D. Flush Mount 110v Power and Dual USB Charge

#FI/CP5/BK - Black



E. Pop-up Wireless Qi Charger with Triple USB Charging

#FI/CP4/BK - Black



F. Cable Port

#FI/CP2/BK - Black

#FI/CP2/SN - Satin Nickel



G. Under Table Dual USB Charging Dock

#FI/CP8/BK - Black



H. Popup Charge & Connect

#FI/CP7/BK - Black



Specify Your Own Device with a Custom Cut-In



CABINET INTERIORS



I. Vertical Rack Mount

#FI/RM/VR/3U

#FI/RM/VR/5U



J. 1RU Vertical, Rack Mounted Cooling Kit

#SA/IVAC



1RU Multi-Port Rack Mounted Power Distribution Unit

#FI/RM/PDU

UNIFI HUDDLE™











2-5 PERSON

Siena style in your choice of finishes with black cabinet top.

30"H

ADA Compliant



Cabinet Finishes	Single Display	Dual Display	No Display	4'x5' Table Top
Warm White Gloss (Laminate)	 D1/338AM1/SN/GW/BK	D1/338AM2/SN/GW/BK	D1/338A/SN/GW/BK	Warm White 3/4" Seamless  TP4860A/S/WW
Slate Gray Matte (Laminate)	 D1/338AM1/SN/SG/BK	D1/338AM2/SN/SG/BK	D1/338A/SN/SG/BK	Slate Gray 3/4" Seamless  TP4860A/S/SG
Gray Oak (Veneer)	 D1/338AM1/SN/GO/BK	D1/338AM2/SN/GO/BK	D1/338A/SN/GO/BK	Satin Black 3/4" Seamless  TP4860A/S/BK
Black Oak (Veneer)	 D1/338AM1/SN/BO/BK	D1/338AM2/SN/BO/BK	D1/338A/SN/BO/BK	Solid Black 1/2" Solid Black Compact Core*  TP4860A/C/BK1
Wengé Oak (Veneer)	 D1/338AM1/SN/WO/BK	D1/338AM2/SN/WO/BK	D1/338A/SN/WO/BK	
Natural Oak (Veneer)	 D1/338AM1/SN/NO/BK	D1/338AM2/SN/NO/BK	D1/338A/SN/NO/BK	

Cabinet: 65"W (1651mm) x 31"H (787mm) (65" (1651mm) w/mount) x 12"D (305mm)

Table: 60"L (1524mm) x 48"W (1219mm) x 29"H (736mm)

UNIFI HUDDLE™ LITE

2-3 PERSON

CAFE
39"H



Single Display

No Display






Warm White 3/4" Seamless	 UHL40AM1/G/S/WW	UHL40A/G/S/WW
Slate Gray 3/4" Seamless	 UHL40AM1/G/S/SG	UHL40A/G/S/SG
Satin Black 3/4" Seamless	 UHL40AM1/G/S/BK	UHL40A/G/S/BK
Solid Black 1/2" Solid Black Compact Core*	 UHL40AM1/G/S/BK1	UHL40A/G/S/BK1


Table: 48"L (1219mm) x 48"W (1219mm) x 39"H (990mm)



Butter-knife Edge
3/4" Seamless
Powder-Coated MDF



Square Edge
1/2" Solid Black (Only)
Compact Core



***Custom HPL Laminates Available**
Call or details.

Specifications

VIDEO CONFERENCE

Display Mounts

Select Table Model

- Universal single or dual display mount with adjustable positions
- Holds displays up to:
 - Huddle: 175 lbs (80 kg)
 - Huddle Light: 110 lbs (50 kg)
- Single: VESA 200 x 200 - 400 x 600
- Dual: VESA 200 x 200 - 500 x 800
- Adjustable Center Line of Screen:
 - 59" (1499mm) / 57" (1448mm) / 55.25" (1403mm) / 53.375" (1356mm) / 51.5" (1308mm)

Speaker/Camera Mount

#FI/SBK

- Fully adjustable height
- Mount above or below display
- Accommodates most video/audio conference systems
- Universal mounting plate pattern: 0-16" (0-410mm)
- Max weight capacity of 25 lbs (11 kgs)

Tech Shelf

#FI/CMS/S - Single Shelf

#FI/CM/D - Dual Shelf

Call for Custom Sizes

- Camera, Speaker, and Controller Shelf
- Fully adjustable height
- Mount above or below display
- Max weight capacity of 5 lbs (2 kgs)
- Single Shelf: 7"W (178mm) x 5.75"D (146mm) x .25"Th (6mm)
- Dual Shelf: 26.25"W (667mm) x 6.75"D (171mm) x .5"Th (13mm)

CABINET INTERIORS

Vertical Rack Mounts

#FI/RM/VR/3U - 3RU

#FI/RM/VR/5U - 5RU

- 3 and 5 rack units of vertical mounted, knob up component storage (total 15RU)
- Threaded for 10-32 screws
- Black powder coated steel
- Lift and load design for easy install
- 10-32 threaded fasteners

1RU Vertical, Rack Mounted Cooling Kit

#SA/IUAC - Black


- Airflow: 40 to 180 CFM | Noise: 9 to 32 dBA
- 180 cfm of airflow at max efficiency maintains a 20 degree rise of up to 3750 btu of electronics
- 19"W (482mm) x 13.5"D (343mm) x 1.75" Th (44mm)
- Probe Length: 72"
- Power Consumption: 8 W, 0.67 A
- Power In: 100 to 240V AC
- RoHS and CE Certified

1RU Multi-Port Rack Mounted Power Distribution Unit

#FI/RM/PDU - Black

- 8 Rear Ports, 1 Front Port
- Maximum Output Current: 15 Amps
- Spike Protection Mode: Line to neutral
- Energy Dissipation: 170 Joules
- Peak Impulse Current: 12,000 Amps
- Maximum Continuous Operating Voltage: 130 VAC RMS
- 9"W (228mm) x 3.75"D (95mm) x 1.75" Th (44mm)
- Safety Agency Listing: cTUVus Certified


CONNECTION PORTS SPECS & CUT-IN LOCATIONS



3" Round Flush mount 110v Power and Dual USB Charge

#FI/CP5/BK - Black


- 1 Outlet, AC 125V 15A max
- 5V 4.2A USB module with 2 ports
- Bore 3" (76.2mm) hole for installation
- 10' (3058mm) SJT 14 AWG*3C power cord
- UL Certified
- Cut-In Locations 1, 2, 3, 5, 6



Pop-up Wireless Qi Charger with Triple USB Charging

#FI/CP4/BK - Black

- Power Input: DC 5V, 6A max
- Wireless Charger: 5 watts max
- USB Charger: 1 x 2.4A (12 watts) max and 2 x 1A (5 Watts) Max
- Wireless Charging Distance: 6mm max
- Qi V1.2.4 Certified
- UL, cUL, FCC ID, RoHS Certified
- Cut-In Locations 1, 2, 3, 4, 5, 6





3-3/8" Round Cable Port

#FI/CP2/BK - Black

#FI/CP2/SN - Satin Nickel

- Split Body Design for Plug and Wire Pass Through
- Cut-In Locations 1, 2, 3, 4, 5, 6


UNIFI HUDDLE



4x6 Popup Charge & Connect

#FI/CP7/BK


- Aluminum Housing
- 1 Grounded AC Outlet, 125 V 12A rating
- 5V 4.2A USB module with 2 ports
- 1 HDMI coupler
- 1 Ethernet RJ45 Coupler power cord
- UL Certified
- Cut-In Locations 1, 2, 3, 4, 5



Under Table Dual USB Charging Dock

#FI/CP8/BK - Black

- Dual 5V DC 2.1A (10.5 Watts) USB charging ports
- Input 5VDC 4.2A wall plug adapter with 8' lead
- Blue LED back-lighting
- UL Pending
- Cut-In Locations 7A, 7B, 7C, 7D




3-3/4" Round Pen Holder

#FI/CP6/BK - Black

#FI/CP6/SA - Satin Aluminum

- Cut-In Locations 1, 2, 3, 4, 5, 6

UNIFI HUDDLE LITE



CUSTOM MADE EASY

Salamander specializes in custom
designing and manufacturing
high-performing furniture solutions
for complex projects.

Call us for a free design consultation.



SALAMANDER DESIGNS

811 Blue Hills Avenue
Bloomfield, CT 06002

salamandercommercial.com

custom@salamanderdesigns.com

800.535.9910



Salamander technology partners provide solutions that, when integrated with the Unifi Huddle, create the perfect interactive, collaboration solutions for every corporate environment.



©2019 Salamander Designs Ltd. v7.19 - 500-111