



Energizer® Vision HD+ Focus Headlamp

HDDIN32EB

The *Energizer*® Vision HD+ Focus headlamp is another innovative headlamp solution within the *Energizer* headlamp line. Featuring LED technology, users get an extraordinarily bright, lightweight hands-free solution with ample run time. Custom optics offer exceptional direct and peripheral vision, making the *Energizer* Vision HD+ Focus a perfect light for home, work and outdoor activities. Featuring patented Digital Focus, users can easily broaden or narrow their field of vision with a simple button press. Memory Recall allows users to quickly access to their favorite focus setting next time the light is activated. With an adjustable head strap, water-resistant design and pivoting head to direct light exactly as needed, *Energizer* continues to deliver innovative lighting solutions.



Provides
315 Lumens
of Light



Provides
Run Time
of 6 Hours



Shines
Light on
Objects 85
Meters
Away



Sustains 1
Meter
Drop Test.



Water resistant
IPX4 - Works
even after
splashing water
on all sides.

DESIGN BENEFITS

- ✓ Patented Digital Focus allows users to broaden or narrow the light beam
- ✓ Red LED mode allows users to preserve night vision
- ✓ Next Push Off to avoid unnecessary switch cycles
- ✓ Compact, lightweight design
- ✓ Water-resistant with shatterproof lens

LIGHT AND POWER SOURCE

- ✓ Features LED Technology
- ✓ Operates on 3 AAA Batteries

ELECTRICAL CHARACTERISTICS

Electrical Characteristics Nominal Power:
Power consumption 3.57W / Batteries AAA
Energizer E92 4.5V dc
LED Specifications: LED 3.0V cc / 1190 mA

CERTIFICATES AND COMPLIANCE

CE RoHS
EMC, EN62471, FCC



This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Tested according to ANSI/NEMA FL1 Standards. Results based on: *Energizer*®, MAX, Alk / E92

PERFORMANCE BENEFITS

- ✓ Memory Recall feature permits to access preferred focus setting the next time the light is switched on
- ✓ Up to 4X brighter than standard LED technology
- ✓ Custom optics deliver exceptional direct and peripheral vision

SPECIFICATIONS

Weight Excluding Batteries:

53 Grams / 1.9 Ounces

Dimensions:

59mm x 49mm x 36mm / 2.3" x 1.9" x 1.4"

NUMBER OF OPERATING MODES: 5

Mode	Lumens	Runtime	Beam Distance
High	315	6	85
Low	20	50	--
Full Spot – Digital Focus	180	12	-
Full Flood – Digital Focus	100	20	-
Red	--	18	-

Before using your flashlight, please read all instructions and cautionary marking on the package and the light.

This datasheet contains information specific to products manufactured at the time publication. Contents do not constitute a claim or warranty.

©2018 Energizer