



SD 4U Splicing fiber Panel, accepts up to 6, 288f FOST Splice Trays, providing up to 1728 fiber mass fusion splicing and 288 single fiber splicing

Product Classification

|                       |   |
|-----------------------|---|
| Portfolio             | CommScope®  |
| Product Series        | SD  |
| Product Type          | Fiber splice panel  |
| Regional Availability | Asia   Australia/New Zealand   EMEA   Latin America   North America |

Dimensions

|        |                      |
|--------|----------------------|
| Depth  | 485.14 mm   19.10 in |
| Height | 177.80 mm   7.00 in  |
| Width  | 482.60 mm   19.00 in |
| Weight | 6.35 kg   14.00 lb   |

Environmental Specifications

|                     |           |
|---------------------|-----------|
| Flammability Rating | UL 94 V-0 |
|---------------------|-----------|

General Specifications

|                |         |
|----------------|---------|
| Rack Units     | 4.0     |
| Shelf Movement | Sliding |
| Color          | Black   |
| Color, front   | Black   |
| Color, rear    | Black   |

Regulatory Compliance/Certifications

|                 |  |
|-----------------|--|
| Agency          | Classification   |
| RoHS 2011/65/EU | Compliant  |
| ISO 9001:2015   | Designed, manufactured and/or distributed under this quality management system |

