

RF Remote Control for Windows 7 & Vista

MODEL NUMBER: ER-V2



Description

The RF Remote for Windows 7 & Vista is a sleek and powerful RF remote control designed specifically for use with Windows 7 & Vista's Media Center multimedia software. It provides more range, convenience and flexibility than infrared remotes.

Features

- **Range:** The RF Remote for Windows Vista provides a range of up to 90 ft (about three times the distance of infrared remotes).
- **Convenience:** Unlike an infrared remote, this RF remote does not require line of sight to the RF receiver. This allows you to manage Media Center from more areas within the room or even from other areas of your house.
- **Flexibility:** Since the RF signal works through walls and furniture, you have more flexibility in locating the PC that will be used to run Media Center. For example, you can place the PC inside an entertainment center cabinet or within an AV closet and still easily control Media Center with the remote.

Highlights

- Controls Media Center in Windows Vista and Windows 7
- Works through walls and furniture
- For Windows 7 & Vista Home Premium and Vista Ultimate

System Requirements

Windows:

- An available USB port
 - Windows 7 Home Premium or Ultimate (64-bit) & Windows Vista Home Premium or Windows Vista Ultimate (32bit or 64bit)
 - TV tuner card with FM radio capability required for live TV and radio functionality
- This remote control is designed specifically for use with Windows Vista Media Center.

Package Includes

- RF Remote Control
- USB RF Receiver
- Printed Quick Start Guide
- Two AA batteries for remote

Specifications

OVERVIEW	
UPC Code	672603045018
Model Frequency	433 Mhz
PRODUCT OVERVIEW	
Product Overview	Keyspan-by-Tripp Lite RF Remote for Windows Vista
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Silver
Shipping Dimensions (hwd / cm)	22.86 x 16.00 x 4.44
Shipping Dimensions (hwd / in.)	9.00 x 6.30 x 1.75
Shipping Weight (kg)	0.34
Shipping Weight (lbs.)	0.75
COMMUNICATIONS	
Signal Range (ft.)	90
Signal Range (m)	27
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>