
2M ULTIMA[™] USB 2.0 A/B CABLE (6.6FT)

29141 | [C2G](#)

FEATURES & BENEFITS

The Ultima USB cable optimizes style, quality, and value in a cable specially designed for high performance. Just plug-and-play for keyboards, mice, modems, printers, and other USB peripherals, and this cable will deliver high speed data transfer up to 480 Mbps. heavy duty 24 AWG power wires provide the proper current to your USB device. Dual foil and braid shielding reduces EMI/RFI interference while twisted pair construction helps reduce crosstalk thus ensuring high speed, error-free data transfer. The sleek design of the molded connectors makes them easy to grip. The metal connector shield helps to meet FCC requirements on EMI/RFI interference, while a solder-to-connector shell and cable braid create an end-to-end shielding solution for a noise-free connection. 24k gold-plated connectors provide maximum corrosion resistance for error-free data transfer. The charcoal gray cable jacket not only matches your case but disappears behind your desk leaving a clean organized look. Finally, an ultra-flexible jacket makes installation easy.

- Supports high speed USB 2.0 devices (480 Mbps), and is backwards compliant with full-speed USB 1.1 (12 Mbps) and low speed USB 1.0 (1.5 Mbps).
- PC and Mac® compatible

SPECIFICATIONS

GENERAL INFO

Color: Grey
Type: USB 2.0 A to B Cables
Component Type: Cables

DIMENSIONS

Height (US): 0.25"
Length (US): 8.5"
Width (US): 5"
Weight: 0.65 lbs

CORD INFORMATION

Connector Type End One: USB-A Male
Connector Type End Two: USB-B Male

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA