

# COMPACT PERFORMANCE SERIES

The CP-T Speaker Series maintains the classic Klipsch signature sound in a sleek, weather-resistant design. Compact, stylish cabinets blend into almost any environment and up-front, one-screwdriver connections make the most efficient use of your valuable time. Unique, front-attach, integrated brackets combined with V-shaped rear profile cabinets allow the speakers to almost disappear tightly in a corner. Exclusive Tractrix® horns provide unmatched low-distortion, highly detailed sound and combine with long-throw woofers for excellent dynamics at any volume level. Solid, talc-filled cabinets with aluminum grilles and stainless steel hardware will make the CP-T Speaker Series your perfect “Everyday Speakers” indoors or out.



## CP-4T COMPACT FULL-RANGE 3.5" 2-WAY

<b>FREQUENCY RESPONSE<sup>1</sup></b> (+/- 3 dB)	100 Hz - 22 kHz
<b>POWER HANDLING<sup>2</sup></b>	5 watts fixed @ 70V   10 watts fixed @ 100V
<b>MAXIMUM SPL<sup>3</sup></b>	94 dB @ 70V   97 dB @ 100V
<b>SENSITIVITY<sup>4</sup></b>	91 dB
<b>TWEETER</b>	.75" (1.9cm) aluminum compression driver
<b>HIGH FREQUENCY HORN</b>	90° x 90° Tractrix® Horn
<b>WOOFER</b>	3.5" (8.9cm) long-throw IMG woofer
<b>CROSSOVER FREQUENCY</b>	3.2kHz
<b>TAP SETTINGS</b>	5 watts fixed @ 70V   10 watts fixed @ 100V
<b>ENCLOSURE TYPE</b>	Bass-reflex via dual front-firing ports
<b>ENCLOSURE MATERIAL</b>	Talc-filled PPC
<b>DIMENSIONS</b>	8.8" (22.4cm) H x 5.5" (14.0cm) W x 4.7" (11.9cm) D
<b>DIMENSIONS WITH WALL MOUNT</b>	8.8" (22.4cm) H x 5.5" (14.0cm) W x 5.5" (14.0cm) D
<b>WEIGHT</b>	4.8 lbs. (2.2kg)
<b>FINISHES</b>	Black/White enclosure and grille
<b>WIRE GAUGE ACCOMODATED</b>	16

SHIPPING QUANTITY: 1 Pair

SHIPPING WEIGHT: 11 lbs

### PART NUMBER

- 1016296 (Black)
- 1060386 (White)

NOTES:

- .75" Aluminum tweeter mated to a 90° x 90° Tractrix® Horn
- 3.5" long-throw woofer
- Front access, one-screwdriver installation of bracket and wiring
- Tool-free angle adjustment

## EASY ONE SCREWDRIVER INSTALLATION

Klipsch Compact Performance Series speakers allow you to attach the bracket to the wall or in the corner, push the speaker onto the first notch of the bracket, channel the wire to the front and attach, handset the desired speaker/bracket angle without additional tools, push the speaker to the last bracket notch and screw down the bracket. Not only a fast, up-front install but gives a clean, uniform look that essentially integrates the speaker and bracket together as one.



## CP-6 T COMPACT FULL-RANGE MULTI-TAP 5.25" 2-WAY

<b>FREQUENCY RESPONSE<sup>1</sup></b> (+/- 3 dB)	83 Hz - 22 kHz
<b>POWER HANDLING<sup>2</sup></b>	75 watts   300 watts peak
<b>MAXIMUM SPL<sup>3</sup></b>	111 dB   117 dB peak
<b>SENSITIVITY<sup>4</sup></b>	94 dB*
<b>NOMINAL IMPEDANCE</b>	8 ohm*
<b>TWEETER</b>	.75" (1.9cm) aluminum compression driver
<b>HIGH FREQUENCY HORN</b>	90° x 90° Tractrix® Horn
<b>WOOFER</b>	5.25" (13.3cm) long-throw IMG woofer
<b>CROSSOVER FREQUENCY</b>	3kHz
<b>TAP SETTINGS</b>	3.75 watts, 7.5 watts, 15 watts, 30 watts @ 70V   7.5 watts, 15 watts, 30 watts @ 100V
<b>ENCLOSURE TYPE</b>	Bass-reflex via dual front-firing ports
<b>ENCLOSURE MATERIAL</b>	Talc-filled PPC
<b>DIMENSIONS</b>	11.0" (27.9cm) H x 7.0" (17.8cm) W x 6.1" (15.5cm) D
<b>DIMENSIONS WITH WALL MOUNT</b>	11.0" (27.9cm) H x 7.0" (17.8cm) W x 6.9" (17.5cm) D
<b>WEIGHT</b>	6.9 lbs. (3.1kg)
<b>FINISHES</b>	Black/White enclosure and grille
<b>WIRE GAUGE ACCOMODATED</b>	16

SHIPPING QUANTITY: 1 Pair

SHIPPING WEIGHT: 17.2 lbs

### PART NUMBER

- 1016298 (Black)
- 1060388 (White)

NOTES:

- .75" Aluminum tweeter mated to a 90° x 90° Tractrix® Horn
- 5.25" long-throw woofer
- Front access, one-screwdriver installation of bracket and wiring

ALSO AVAILABLE  
CP-6: Low impedance version