

PROFESSIONAL SERIES REFERENCE

Using the same acoustic components and horn material as the highly acclaimed Reference Premiere box speaker line, the Professional Reference Series perfectly combines the aesthetics of an architectural speaker with the pure performance and dynamic voicing of the Reference series.

- True Reference acoustics • SecureFit™ Installation System • Minimal footprint models available



IN-WALL



- In-wall LCR speaker for home theater or 2-channel listening
- SecureFit™ Installation System
- Flat, magnetic grille
- PVC Paint Shield included

PRO-25RW LCR DUAL 5.25" IN-WALL LCR SPEAKER

FREQUENCY RESPONSE	50Hz-23kHz +/- 3dB
SENSITIVITY	93dB @ 2.83V/1 meter
IMPEDANCE	8 ohms compatible
POWER HANDLING (CONT/PEAK)	75W /300W
HIGH FREQUENCY DRIVER	1" (2.54cm) aluminum dome tweeter mated to a 90°x90° Tractrix® Horn
LOW FREQUENCY DRIVER	Dual 5.25" (16.51cm) IMG woofers
DIMENSIONS	7.65" W x 17.53" H x 3.81" D (19.4cm H x 44.5cm W x 9.7cm D)
MOUNTING DEPTH	3.68" (9.3cm)
CUTOUT DIMENSIONS	6.5" W X 16.38" H (16.5cm W X 41.6cm H)
WEIGHT	6.5 lbs. (2.95kg)
INSTALLATION KIT	IK-502-W or IK-502-W II (sold separately)

SHIPPING QUANTITY:	Single
SHIPPING WEIGHT:	3.5 kg 7.7 lbs
PART NUMBER	1064445



NOTES:



- In-wall speaker for home theater, distributed audio or 2-channel listening
- SecureFit™ Installation System
- Flat, magnetic grille
- PVC Paint Shield included

PRO-18RW 8" IN-WALL SPEAKER

FREQUENCY RESPONSE	56Hz-23kHz +/- 3dB
SENSITIVITY	95dB @ 2.83V/1 meter
IMPEDANCE	8 ohms compatible
POWER HANDLING (CONT/PEAK)	50W /200W
HIGH FREQUENCY DRIVER	1" (2.54cm) aluminum dome tweeter mated to a 90°x90° Tractrix® Horn
LOW FREQUENCY DRIVER	8" (20.32cm) IMG woofer
DIMENSIONS	10.3" W x 15.89" H x 4.0" D (26.2cm H x 40.4cm W x 10.2cm D)
MOUNTING DEPTH	3.88" (9.9cm)
CUTOUT DIMENSIONS	9.13" W X 14.72" H (23.2cm W X 37.4cm H)
WEIGHT	7.9 lbs. (3.6kg)
INSTALLATION KIT	IK-800-W or IK-800-W II (sold separately)

SHIPPING QUANTITY:	Single
SHIPPING WEIGHT:	4.1 kg 9 lbs
PART NUMBER	1064444



NOTES:



IK-650-C II INSTALLATION BRACKET FOR 6.5" IN-CEILING SPEAKER

SHIPPING QUANTITY	10-Pack
SHIPPING WEIGHT	4.5 kg 10 lbs
FOR USE WITH	PRO-160RPC, PRO-16RC, DS-160C, DS-160CDT, DS-160CSM, CS-16C II, CS-16CSM

PART NUMBER	1065321
-------------	---------



IK-650-W INSTALLATION BRACKET FOR 6.5" IN-WALL SPEAKER

SHIPPING QUANTITY	Pair
SHIPPING WEIGHT	0.9 kg 2 lbs
FOR USE WITH	PRO-160RPW, PRO-16RW

PART NUMBER	1001177
-------------	---------



IK-650-W II INSTALLATION BRACKET FOR 6.5" IN-WALL SPEAKER

SHIPPING QUANTITY	10-Pack
SHIPPING WEIGHT	4.5 kg 10 lbs
FOR USE WITH	PRO-160RPW, PRO-16RW, DS-160W, CS-16W

PART NUMBER	1065323
-------------	---------



IK-502-W INSTALLATION BRACKET FOR DUAL 5.25" IN-WALL LCR SPEAKER

SHIPPING QUANTITY	Pair
SHIPPING WEIGHT	0.9 kg 2 lbs
FOR USE WITH	PRO-250RPW LCR, PRO-25RW LCR

PART NUMBER	1009682
-------------	---------



IK-502-W II INSTALLATION BRACKET FOR DUAL 5.25" IN-WALL LCR SPEAKER

SHIPPING QUANTITY	Pair
SHIPPING WEIGHT	0.9 kg 2 lbs
FOR USE WITH	PRO-250RPW LCR, PRO-25RW LCR, DS-250W LCR

PART NUMBER	1065325
-------------	---------



IK-402-W INSTALLATION BRACKET FOR DUAL 4" IN-WALL LCR SPEAKER

SHIPPING QUANTITY	Pair
SHIPPING WEIGHT	0.9 kg 2 lbs
FOR USE WITH	PRO-24RW LCR

PART NUMBER	1065328
-------------	---------



IK-400-C INSTALLATION BRACKET FOR 3.5" IN-CEILING SPEAKER

SHIPPING QUANTITY	Pair
SHIPPING WEIGHT	0.9 kg 2 lbs
FOR USE WITH	PRO-14RC

PART NUMBER	1065329
-------------	---------



IK-400-W INSTALLATION BRACKET FOR 4" IN-WALL SPEAKER

SHIPPING QUANTITY	Pair
SHIPPING WEIGHT	0.9 kg 2 lbs
FOR USE WITH	PRO-14RW

PART NUMBER	1065329
-------------	---------