

## 6.5" Two-Way In-Wall Loudspeaker



# R-2650-W

The affordable R-2650-W in-wall loudspeaker makes discrete audio a convincing reality for almost anyone. Built to the same exacting standards as all Klipsch products, this high-performance model doesn't suffer from the design shortcuts and sonic compromises that plague competing designs.

This exceptional speaker employs a 6.5-inch gray polymer woofer cone and 1-inch soft/silk dome tweeter to deliver mind-bending depth and clarity. By incorporating our patent-pending KWIC-Lock™ two-screw frame design, the R-2650-W is also one of the most easy-to-install products on the market. This "one trip up the ladder" concept significantly reduces the time it takes to complete an installation job.

Available in a white finish, the R-2650-W can be paired with one of Klipsch's new installation kits (sold separately). Each of these revolutionary kit designs allow for increased mounting flexibility and incorporate a mud ring, wire tie and universal metal mesh wing for multi-position placement and a color-coded bracket for easy speaker size identification.

- Good sensitivity and power handling
- KWIC-lock mounting mechanism
- Single piece grille frame and rustproof aluminum grille
- IR receiver knock out
- Weatherized components

### SPECIFICATIONS

FREQUENCY RESPONSE	65Hz-20kHz ± 3dB
SENSITIVITY	91dB @ 1 watt/1 meter
NOMINAL IMPEDANCE	8 ohms
CROSSOVER FREQUENCY	1800Hz
POWER HANDLING	50 watts (200 watts peak)
ENCLOSURE MATERIAL/TYPE	ABS/ Infinite baffle, front flush with wall
DRIVE COMPONENTS	Two-way system using one 1" (2.54cm) silk dome tweeter and one 6.5" (16.51cm) polymer woofer
WIRE GAUGE ACCOMMODATED	12
WEIGHT	7.2 lbs. (3.25kg)
HEIGHT	14.3" (36.32cm)
WIDTH	9.3" (23.62cm)
MOUNTING DEPTH	3.75" (9.5cm)
CUTOUT DIMENSIONS	13" (33.02cm) x 8" (20.32cm)
FINISH	White
INSTALLATION KIT	IK-650-W (sold separately)

www.klipsch.com  
1-800-KLIPSCH

