

## Nuvo® P300 Player Preamplifier

Embrace more opportunities, explore more options, with the Nuvo P300 Player Preamplifier. Designed to connect with the latest A/V equipment, the P300 delivers the expansive streaming variety and stunning quality of the Player Portfolio to specialized power components. Maximizing performance, while integrating fully and easily into a Player Portfolio system, the Player Preamplifier takes Legrand's flexibility to the next level.



- All your favorite music is right at your fingertips with easy access to networked computers, streaming Internet Radio, and even audio content stored on an Android or iOS device.
- Compatible with Legrand's other Nuvo Player Portfolio products for a truly custom, easily expandable system (up to sixteen zones).
- Supports both wired Ethernet and wireless 802.11n configuration options adding flexibility for any home.
- Includes 802.11n wireless capability and utilizes both 2.4 and 5 Ghz bands, for fast signals and broad coverage.
- Connect to storage devices, analog equipment, or home theater receivers through the unit's audio line-in, line-out, Mini-TOSLINK fiber optic digital input and output, or USB ports.
- Manage your music via the convenient wall-mounted P10 keypad or wirelessly from the palm of your hand with free apps for your Apple or Android device.
- Attractive contemporary industrial design discreetly fits into small spaces.

Streaming services subject to geographic availability.

# Nuvo® P300 Player Preamplifier

## SPECIFICATIONS

### Input/Output Connectors

Line Input	1 - TRS 3.5 mini TOSLINK Combo Receiver
Line Output	1 - TRS 3.5 mini TOSLINK Combo Receiver
USB 2.0 Connection (Type A)	1
Local Area Network (LAN)	1 - RJ45

### Supported Audio Formats

Music Files (via USB or network):	MP3
	WMA
	AAC
	Ogg Vorbis
	FLAC
	WAV

Internet Radio:	Pandora
	Sirius/XM
	iHeart Radio
	Spotify
	TuneIn
	Deezer
	Napster

Playlist Support:	WPL
	M3U
	PLS
	iTunes

### IP Control

Apple iPod®
Apple iPhone®
Apple iPad®
Android Mobile
Android Tablet

### Network Connectivity

LAN (Wired Connection)	10/100base-t Ethernet
Wireless Connection	MIMO, 2 TX + 2 RX Channels
	IEEE 802.11a/b/g/n
	Wi-Fi Alliance CERTIFIED™

### Line Output - Digital:

Sample Rates	44.1 KHz-192KHz
Bit Rate	24B
Signal-to-Noise Ratio at rated output	>120 dB SNR
THD+n	<0.0005%
Frequency Response	+/-0.1 dB 20 Hz to 20 KHz

### Line Input - Digital:

Sample Rates	44.1 KHz-192KHz
Bit Rate	24B
Signal-to-Noise Ratio at rated output	>120 dB SNR
THD+n	<0.0005%
Frequency Response	+/-0.1 dB 20 Hz to 20 KHz

### Line Output - Analog:

Output Level	0-2.0 V RMS
Output Impedance	5 Ohms
Signal-to-Noise Ratio, rated output	>100 dB SNR
THD+n	<0.005%
Frequency Response	+/- 0.5 dB 20 Hz to 20 KHz

### Line Input - Analog:

Input Impedance	10 KOhms
Input Overload	2.0 V RMS
Signal-to-Noise Ratio, rated output	>100 dB SNR
THD+n	<0.005%
Frequency Response	+/- 0.5 dB 20 Hz to 20 KHz

### Audio Processing

Bass Equalization	+/-12 dB range
Treble Equalization	+/-12 dB range
Balance	

### Regulatory Approvals

Safety	cTUVus, CE-LVD
EMC	FCC, IC, CE-EMC, C-Tick
Environmental Compliance	RoHS

### Power Requirements

Input Voltage	100 – 240VAC, 50/60 Hz
Power Consumption (max)	10 W
Power Consumption (typical)	5.1 W

### Operating Temperature

0° C to 40° C

### Physical Specifications

Unit Size (mm)	38 H x 145.5 W x 90.5 D
Unit Size (inch)	1.5 H x 5.73 W x 3.56 D
Unit Weight (kg)	0.2
Unit Weight (pounds)	0.5

### Shipping Specifications

Unit Size (mm)	240 D x 230 W x 65.5 H
Unit Size (inch)	9.45 D x 9.06 W x 2.58 H
Unit Weight (kg)	1.30
Unit Weight (pounds)	2.87

### Languages Supported

English, Spanish, French  
Portuguese, German, Italian

Legrand reserves the right to change specifications without notice.

designed to be better™



Legrand, North America

3015 Kustom Drive  
Hebron, KY 41048  
United States  
844.334.8044  
www.legrand.us/nuvo