

Power Amplifier Output

Continuous Average Output Power	40W (20W x 2
Both channels	1kHz / 1% THD
Rated Distortion (1/2 power)	0.40%
Rated Impedance	4 ohms
Frequency Response (20-20kHz)	±2 dB

Source Input

Front	3.5mm Stereo Jack
Input Impedance	20k ohms
Input Sensitivity for Rated Power	300mV RMS
Back; Variable Input	Screw Terminal
Input Impedance	20K ohms
Input Sensitivity for Rated Power	300mV RMS
Back; Fixed Input	Screw Terminal
Input Impedance	20K ohms
Input Sensitivity for Rated Power	300mV RMS

Power Requirements

Power Supply	16VDC
Power Consumption at maximum available output	45W
Power Consumption with music (typical)	10W
Power Consumption no signal	2.1W
Power Consumption standby	0.5W
Auto shut-off time	20 mins.

Regulatory Approvals

CE-EMC (EU), FCC (USA and Canada)

Physical Specifications

Unit Size (mm)	50 H x 50 W x 29 D
Unit Size (inch)	1.97 H x 1.97 W x 1.14 D
Shipping Size (mm)	424 H x 306 W x 395 D
Shipping Size (inch)	16.7 H x 12 W x 15.5 D
Unit Weight (kg)	0.11
Unit Weight (lbs)	0.24
Shipping Weight (kg)	7.0
Shipping Weight (lbs)	15.4

Speaker

Electrical

Power	10 ~50W
Impedance	4 ohms

Physical Specifications

Unit Size (mm)	190 H x 160 W x 90 D
Unit Size (inch)	7.5 H x 6.3 W x 3.54 D
Shipping Size (mm)	400 H x 350 W x 245 D
Shipping Size (inch)	15.75 H x 13.78 W x 9.65 D

Remote Control

Electrical

IR Frequency	38.7 kHz
Batteries	AAA x 2

Physical Specifications

Unit Size (mm)	110 H x 42 W x 14 D
Unit Size (inch)	4.33 H x 1.65 W x 0.55 D
Shipping Size(mm)	296 H x 245 W x 280 D
Shipping Size (inch)	11.65 H x 9.65 W x 11 D

NuVo reserves the right to change specifications without notice.