



Multi-technology readers



Overview

Schlage® multi-technology readers are designed to simplify your access control solutions and allow a transition from existing population proximity or magnetic stripe to more secure encrypted card technology at your own pace—without having to change readers as new technologies are available. Five available models to fit any need and works with multiple form factors including wristbands, cards, fobs and tags.

MT11: Mullion Mount

MT15: Wall Mount (Single-gang)

MTK15: Wall Mount w/keypad (Single gang) MTMS15: Magnetic Stripe Reader Wall Mount

 $MTMSK15: Magnetic\ Stripe\ Reader\ Wall\ Mount\ with\ Keypad$

Features and benefits

Schlage multi-technology readers contain both 125 kHz proximity and 13.56 MHz contactless smart card capability in one-unit handling multiple formats simultaneously. Wiegand and RS-485 output available for simple interface with most access control panels.

- Compatible with NFC-open smart phones using Schlage or aptiQ mobile credentials.
- Limited lifetime warranty
- Accommodates interior, exterior, metal and non-metal installation environments
- Quick-connect cable allows for easy installation
- Easy-to-install mounting bracket
- Available finishes include: Black (standard), cool-tone gray, cream and warm-tone brown











Model*	MT11		MT15	MTK15	MTMS15	MTMSK15
Reader type	Multi-technology mullion	-	Multi-technology – single gang	Multi-technology with keypad –single gang	Multi-technology with magnetic stripe	Multi-technology with magnetic stripe and keypad
Frequency			13.56 MHz and 125 kHz —		■ 13.56 MHz and 125 k	Hz and magnetic stripe—
FIPS 201 compliant				Yes —		
Standard default PIV output	-			75 bit PIV**		
Standards				SO 14443A, 14443B, 156	93	
Certifications	FCC Certification • IC Certification • UL 294 Listed • RED Directive (15 EU Countries) • CE Mark • IP65					
Voltage range	5-16 VDC —					
Power supply				Linear DC		
Current requirement	MT11 M	T11-485	MT15 & MT15-485	MTK15 and MTK15-485	MTMS15 and MTMS15-485	MTMSK15 and
(at 12 VDC and	Avg. 100 mA Av	vg. 115 mA	Avg. 120 mA	Avg. 120 mA	Avg. 120mA	MTMSK15-485 Avg. 120mA
25 C; mAmps)	Peak 170 mA Pe	eak 145 mA	Peak 200 mA	Peak 230 mA	Peak 200mA	Peak 230mA
Read range				oximity: Up to 5" (12.7 cm)		
	MIFARE Classic: Up to 4" (10 cm)					
	MIFARE Plus: Up to 1" (2.5 cm) MIFARE DESFire EV1: Up to 2" (5.1 cm)					
	PIV credential: Up to 2.5" (6.5 cm)					
Cable specification			18 A	WG, 5 conductor stranded	/shielded	
System interfaces				nd / Clock & Data / RS-48		
Cabling distance			Wiegand output: 500 ft (152 m)			
Physical dimensions	5.91" x 1.72" x 0.8	1"	5.1" x 3.25" x 0.76"	5.1" x 3.25" x 0.76"	4.43" x 5.17" x 1.15"	4.43" x 5.17" x 1.15"
(HxWxD)	15 cm x 4.4 cm x 2	-		12.9 cm x 8.3 cm x 1.9 cm		11.25 cm x 13.13 cm x 2.92 cm
Operating temperatures	-40° to 158°F		-40° to 158°F	-40° to 158°F	-31° to 151°F	-31° to 151°F
	(-40° to 70°C)		(-40° to 70°C)	(-40° to 70°C)	(-35° to 67°C)	(-35° to 67°C)
Weight	5.7 oz		9.1 oz	9.3 oz	8.9 oz	9.5 oz
Material				PBT Polymer		
Technologies supported in d	efault mode					
Schlage Proximity			•			•
XceedID® Proximity	•		•		•	•
HID® Proximity				•		•
GE/CASI ProxLite®				•		•
AWID® Proximity	•			•		•
LenelProx®			•	•		•
Schlage/aptiQ mobile			•	•	•	•
Schlage/aptiQ/XceedID						
smart cards using MIFARE Classic	•		•	•	•	•
Schlage smart cards using MIFARE Plus	•		•	•	•	•
Schlage/aptiQ smart cards using MIFARE DESFire EV1			•	•	•	•
DESFire® CSN	•		•	•	•	•
HID iCLASS® CSN	•		•	•	•	•
Inside Contactless PicoTag® CSN	•		•	•	•	•
ST Microelectronics® CSN	•		•	•		•
Texas Instruments Tag-It® CSN	•		•	•	•	•
Phillips I-Code® CSN			•	•	•	
Color	Black (standard) * Some features and benefits listed on the front may not be applicable to the smart-only and proximity-only readers. ** Other output options available through configuration.					
options [†]	*** RS-485 model numbers include "-485" after the original model number. For example, MTII-485 is the RS-485 wersion of the multi-technology mini-mullion reader. Multi-drop, Open Standard Device Protocol (OSDP). † Lead time may apply for non-standard colors					

About Allegion

Allegion (NYSE: ALLE) is a global pioneer in safety and security, with leading brands like CISA, Interflex, LCN, Schlage, SimonsVoss and Von Duprin. Focusing on security around the door and adjacent areas, Allegion produces a range of solutions for homes, businesses, schools and other institutions. Allegion is a \$2 billion company, with products sold in almost 130 countries. For more, visit www.allegion.com.

