



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





# NOTES:

1. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE USE WITH THIS PRODUCT.
2. ALL CATEGORY 6A, RJ45, 10GB/S, 8-POSITION, 8-WIRE SHIELDED KEYSTONE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
3. TERMINATES 22-24 AWG SOLID OR STRANDED SHIELDED AND UN-SHIELDED CABLE IN A HORIZONTAL MANNER.
4. SEE INSTALLATION INSTRUCTIONS FOR PROPER TERMINATION METHOD.
5. CAP (TERMINATION BLOCK) IS CODED FOR T568A AND T568B WIRING MAPPING SCHEMES.
6. PART INCLUDES:
  - A. MODULE HOUSING: DIECAST/PLATED, INTERNAL COMPONENTS MADE FROM VARIOUS MATERIALS.
  - B. CAP (TERMINATION BLOCK): PLASTIC /WHITE IN COLOR W/ PAD PRINTED WIRE MAPPING SCHEMES.
  - C. CABLE TIE: PLASTIC/NYLON/RAW COLOR (NOT SHOWN IN DRAWING FIGURES).
  - D. COPPER FOIL TAPE: COPPER
7. WEIGHT: 6.67 LBS/100 PCS [ 3027 grams/100 PCS ]
8. DIMENSIONS IN [ ] ARE METRIC.
9. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIALS RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPATION COMMITTEE.

RETENTION  
CAP



MODULE  
HOUSING



.65  
[ 16.5 ]  
REF

PART NUMBER		KJS6X88TC	
TITLE		CATEGORY 6A RJ45 10GB/S 8-POSITION 8-WIRE SHIELDED KEYSTONE JACK MODULE (CABLE RANGE 22-24 AWG)	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		00326EAA-DC/01C	
THIRD ANGLE PROJECTION		PANDUIT	
MATERIAL		DRAWING NUMBER	
SEE NOTE 6		00326EAA-DC	
DRAWN BY	DATE	CHK	SCALE
BJN	09-14-18	DCS	FULL
SHEET 1 OF 1			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01C	10-23-18	BJN	DCS	RWI	UPDATED	0326EAA-DC