

# AXIS Camera Station S2216 Appliance

All-in-one recorder with integrated 16 channel PoE switch for high-definition surveillance

AXIS Camera Station S2216 Appliance is an all-in-one recording solution with integrated, manageable PoE switch designed to deliver reliable high-definition surveillance with up to 4K resolution. For quick and easy installation, AXIS S2216 is preconfigured and preloaded with AXIS Camera Station video management software, and includes licenses for 16 channels plus all necessary system software. AXIS Camera Station offers an intuitive user interface that allows users to take full advantage of Axis wide range of video surveillance cameras and other IP products. With the operating system stored on a solid-state drive (SSD) and 3-year hardware warranty, AXIS S2216 provides a reliable surveillance solution.

- > **All-in-one solution with integrated PoE switch**
- > **High-definition surveillance with up to 4K resolution**
- > **AXIS Camera Station licenses included**
- > **Full compatibility with Axis products**



## AXIS Camera Station S2216 Appliance

<b>Licenses</b>	Includes 16 AXIS Camera Station Core Device licenses	1x SFP 10/100/1000 Mbps 1x RJ45 10/100/1000 Mbps
<b>Processor</b>	Intel® Core i5	<b>Rear side Server:</b>
<b>Memory</b>	8 GB RAM	1x RJ45 10/100/1000 Mbps
<b>Storage</b>	8 TB (2x4 TB) Surveillance Class HDD Additional storage: 8 TB (2 free bays) RAID levels: 0, 1, 5	2x USB 2.0 1 Displayport™ 1 HDMI port
<b>Switch</b>	16 ports integrated, 260 W total power budget Power over Ethernet (PoE) IEEE 802.3at Class 4	<b>Operating conditions</b>
<b>Graphic card</b>	Intel® HD Graphics 630	0 °C to 40 °C (32 °F to 104 °F) Humidity: 10–90% RH (non-condensing)
<b>Operating system</b>	Microsoft® Windows® 10 IoT Enterprise Operating system recovery: yes Operating system drive: 120 GB SSD	<b>Storage conditions</b>
<b>Video streaming</b>	<b>Live view:</b> 1 x 4K stream full screen 4 split x 1080p Up to 16 cameras split view Supports two monitors, maximum one 4K monitor recommended <b>Playback:</b> Supports the same split scenarios as live view Supports only one monitor	–40 °C to 65 °C (–40 °F to 149 °F)
<b>Recording</b>	Qualified for recording with a total recording rate up to 384 Mbit per second	<b>Approvals</b>
<b>Power</b>	Max 520 W, 260 W PoE dedicated 100 – 240 V AC, 6.5–2.5 A, 50/60 Hz	EMC CNS 13438, EAC, EN 55024, EN 55032 Class A, EN 61000-3-2, EN 61000-3-3, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A, ICES-003 Class A, KC KN32 Class A, KC KN35, RCM AS/NZS CISPR 32 Class A, VCCI Class A
<b>Connectors</b>	<b>Front side:</b> 1x USB 3.0 1x Audio line in 1x Audio line out <b>Rear side Switch:</b> 16x PoE ports 10/100 Mbps	<b>Safety</b> IEC/EN 60950-1, IEC/EN 62368-1, KC-Mark, UL 62368-1, IS 13252
		<b>Dimensions</b>
		476 x 440 x 45 mm (18.7 x 17.3 x 1.8 in), 1U chassis
		<b>Weight</b>
		11 kg (24.3 lb)
		<b>Included accessories</b>
		Rack rails, power cord
		<b>Optional accessories</b>
		Surveillance Hard Drive 4 TB available from Axis Axis desktop terminals Axis Ethernet surge protector For more accessories, see <a href="http://axis.com">axis.com</a>
		<b>Warranty</b>
		Axis 3-year warranty and AXIS Extended Warranty option, see <a href="http://axis.com/warranty">axis.com/warranty</a>

## AXIS Camera Station

For details about AXIS Camera Station features and functions, see the AXIS Camera Station datasheet on [axis.com](http://axis.com)

Environmental responsibility:

[axis.com/environmental-responsibility](http://axis.com/environmental-responsibility)