

**RATCHETING SQUARE DRIVE HEADS - SAE**

Square Drive (Inches)	J (0.425")	Max Torque Ft. Lbs.	Y (0.560")	Max Torque Ft. Lbs.	X (0.735")	Max Torque Ft. Lbs.	Z (0.990")	Max Torque Ft. Lbs.	Z Dual Pins	Max Torque Ft. Lbs.
1/4	TCQJD8A-72	60								
3/8	TCQJD12A-80	60	TCQYD12A-80	100						
1/2	TCQJD16A	60	TCQYD16A	240	TCQXD16A	240				
3/4					TCQXD24A	240	TCQZD24B	480	TCQZD24BDP	480
1					TCQXD32A	240	TCQZD32B	480	TCQZD32BDP	480



Z Shank Dual Pins



TCQJD16A

**FIXED SQUARE DRIVE HEADS - SAE**

Square Drive (Inches)	J (0.425")	Max Torque Ft. Lbs.	Y (0.560")	Max Torque Ft. Lbs.	X (0.735")	Max Torque Ft. Lbs.	Z (0.990")	Max Torque Ft. Lbs.	Z Dual Pins	Max Torque Ft. Lbs.
1/4	TCQJSD8A	60								
3/8	TCQJSD12A	60	TCQYSD12A	100						
1/2	TCQJSD16A	60	TCQYSD16A	240	TCQXSD16A	240				
3/4					TCQXSD24A	240	TCQZSD24A	480	TCQZSD24ADP	480
1					TCQXSD32A	240	TCQZSD32A	480		



TCQJSD8A

**OPEN END HEADS - SAE**

Square Drive (Inches)	J (0.425")	Max Torque Ft. Lbs.	Y (0.560")	Max Torque Ft. Lbs.	X (0.735")	Max Torque Ft. Lbs.	Z (0.990")	Max Torque Ft. Lbs.	Z Dual Pins	Max Torque Ft. Lbs.
1/4	TCQJO8A	5								
9/32	TCQJO9A	7								
5/16	TCQJO10A	9								
3/8	TCQJO12A	18								
7/16	TCQJO14A	26								
1/2	TCQJO16A	34								
9/16	TCQJO18A	58	TCQYO18A	58						
5/8	TCQJO20A	60	TCQYO20A	70						
11/16	TCQJO22A	60	TCQYO22A	99						
3/4	TCQJO24A	60	TCQYO24A	125	TCQXO24A	125				
13/16	TCQJO26A	60	TCQYO26A	160	TCQXO26A	164				
7/8	TCQJO28A	60	TCQYO28A	160	TCQXO28A	193				
15/16	TCQJO30A	60	TCQYO30A	160	TCQXO30A	200				
1	TCQJO32A	60	TCQYO32A	160	TCQXO32A	240	TCQZO32A	298	TCQZO32ADP	298
1 1/16	TCQJO34A	60	TCQYO34A	160	TCQXO34A	240	TCQZO34A	321	TCQZO34ADP	321
1 1/8	TCQJO36A	60	TCQYO36A	160	TCQXO36A	240	TCQZO36A	367	TCQZO36ADP	367
1 3/16			TCQYO38A	160	TCQXO38A	240	TCQZO38A	433	TCQZO38ADP	433
1 1/4	TCQJO40A	60	TCQYO40A	160	TCQXO40A	240	TCQZO40A	480	TCQZO40ADP	480
1 5/16			TCQYO42A	160	TCQXO42A	240	TCQZO42A	480	TCQZO42ADP	480
1 3/8	TCQJO44A	60	TCQYO44A	160	TCQXO44A	240	TCQZO44A	480	TCQZO44ADP	480
1 7/16			TCQYO46A	160	TCQXO46A	240	TCQZO46A	480	TCQZO46ADP	480
1 1/2	TCQJO48A	60	TCQYO48A	160	TCQXO48A	240	TCQZO48A	480	TCQZO48ADP	480
1 9/16			TCQYO50A	160	TCQXO50A	240	TCQZO50A	480	TCQZO50ADP	480
1 5/8	TCQJO52A	60	TCQYO52A	160	TCQXO52A	240	TCQZO52A	480	TCQZO52ADP	480
1 11/16					TCQXO54A	240	TCQZO54A	480	TCQZO54ADP	480
1 3/4			TCQYO56A	160	TCQXO56A	240	TCQZO56A	480	TCQZO56ADP	480
1 13/16					TCQXO58A	240	TCQZO58A	480	TCQZO58ADP	480
1 7/8			TCQYO60A	160	TCQXO60A	240	TCQZO60A	480	TCQZO60ADP	480
2					TCQXO64A	240	TCQZO64A	480	TCQZO64ADP	480
2 1/16							TCQZO66A	480	TCQZO66ADP	480
2 1/8					TCQXO68	240	TCQZO68A	480	TCQZO68ADP	480
2 1/4			TCQY072	160			TCQZO72A	480	TCQZO72ADP	480
2 3/8									TCQZO76ADP	480
2 1/2			TCQY080	160			TCQZO80A	480	TCQZO80ADP	480
2 3/4							TCQZO88A	480		
3							TCQZO96A	480		



TCQJO16A



TCQZO36ADP

Center of fastener to retaining pin:

TCQJ Series - 2.50"

TCQY Series - 3.00"

TCQX Series - 4.50"

TCQZ Series - 5.75"

