

**12-POINT BOX END 15° OFFSET HEADS - SAE**

Square Drive (Inches)	J (.425")	Max Torque Ft. Lbs.	Y (.560")	Max Torque Ft. Lbs.	X (.735")	Max Torque Ft. Lbs.	Z (.990")	Max Torque Ft. Lbs.	Z Dual Pins	Max Torque Ft. Lbs.
1/4	TCQJX8A	18								
9/32	TCQJX9A	41								
5/16	TCQJX10A	41								
3/8	TCQJX12A	60								
7/16	TCQJX14A	60								
1/2	TCQJX16A	60	TCQYX16A	75						
9/16	TCQJX18A	60	TCQYX18A	112						
5/8	TCQJX20A	60	TCQYX20A	160	TCQXX20A	171				
11/16	TCQJX22A	60	TCQYX22A	160	TCQXX22A	200				
3/4	TCQJX24A	60	TCQYX24A	160	TCQXX24A	219				
13/16	TCQJX26A	60	TCQYX26A	160	TCQXX26A	240			TCQZX26ADP	275
7/8	TCQJX28A	60	TCQYX28A	160	TCQXX28A	240				
15/16	TCQJX30A	60	TCQYX30A	160	TCQXX30A	240	TCQZX30A	300		
1	TCQJX32A	60	TCQYX32A	160	TCQXX32A	240				
1 1/16	TCQJX34A	60	TCQYX34A	160	TCQXX34A	240	TCQZX34A	480	TCQZX34ADP	300
1 1/8			TCQYX36A	160	TCQXX36A	240	TCQZX36A	480	TCQZX36ADP	480
1 3/16			TCQYX38A	160	TCQXX38A	240	TCQZX38A	480	TCQZX38ADP	480
1 1/4			TCQYX40A	160	TCQXX40A	240	TCQZX40A	480	TCQZX40ADP	480
1 5/16			TCQYX42A	160	TCQXX42A	240	TCQZX42A	480	TCQZX42ADP	480
1 3/8					TCQXX44A	240	TCQZX44A	480		
1 7/16			TCQYX46A	160	TCQXX46A	240	TCQZX46A	480	TCQZX46ADP	480
1 1/2			TCQYX48A	160	TCQXX48A	240	TCQZX48A	480	TCQZX48ADP	480
1 9/16			TCQYX50A	160	TCQXX50A	240	TCQZX50A	480	TCQZX50ADP	480
1 5/8			TCQYX52A	160	TCQXX52A	240	TCQZX52A	480	TCQZX52ADP	480
1 11/16					TCQXX54A	240	TCQZX54A	480	TCQZX54ADP	480
1 3/4					TCQXX56A	240	TCQZX56A	480	TCQZX56ADP	480
1 13/16					TCQXX58A	240	TCQZX58A	480	TCQZX58ADP	480
1 7/8					TCQXX60A	240	TCQZX60A	480	TCQZX60ADP	480
2					TCQXX64A	240	TCQZX64A	480	TCQZX64ADP	480
2 1/16							TCQZX66A	480	TCQZX66ADP	480
2 1/8							TCQZX68A	480	TCQZX68ADP	480
2 3/16									TCQZX70ADP	480
2 1/4							TCQZX72A	480	TCQZX72ADP	480
2 3/8									TCQZX76ADP	480
2 1/2							TCQZX80A	480	TCQZX80ADP	480



Z Shank Dual Pins



TCQJX18A

TORQUE TOOLS

HEADS



**12-POINT BOX END 0° OFFSET - SAE**

Square Drive (Inches)	J (.425")	Max Torque Ft. Lbs.	Y (.560")	Max Torque Ft. Lbs.
3/8	TCQJXD12A	60		
7/16	TCQJXD14A	60		
1/2	TCQJXD16A	60		
9/16	TCQJXD18A	60		
5/8			TCQYXD20A	160
11/16	TCQJXD22A	60	TCQYXD22A	160
3/4	TCQJXD24A	60	TCQYXD24A	160
7/8	TCQJXD28A	60	TCQYXD28A	160
15/16	TCQJXD30A	60	TCQYXD30A	160
1	TCQJXD32A	60		



TCQJXD24A

