




12-POINT BOX END 15° OFFSET - METRIC



Z Shank Dual Pins



TCQJXM14A

Square Drive (mm)	J (0.425")	Max Torque Ft. Lbs.	Y (0.560")	Max Torque Ft. Lbs.	X (0.735")	Max Torque Ft. Lbs.	Z (0.990")	Max Torque Ft. Lbs.	Z Dual Pins	Max Torque Ft. Lbs.
6	TCQJXM6A	15								
7	TCQJXM7A	20								
8	TCQJXM8A	22								
9	TCQJXM9A	30								
10	TCQJXM10A	53								
11	TCQJXM11A	59								
12	TCQJXM12A	60								
13	TCQJXM13A	60	TCQYXM13A	75						
14	TCQJXM14A	60	TCQYXM14A	117						
15	TCQJXM15A	60	TCQYXM15A	148						
16	TCQJXM16A	60	TCQYXM16A	160	TCQXXM16A	183				
17	TCQJXM17A	60	TCQYXM17A	160	TCQXXM17A	197				
18	TCQJXM18A	60	TCQYXM18A	160	TCQXXM18A	224				
19	TCQJXM19A	60	TCQYXM19A	160	TCQXXM19A	238				
20	TCQJXM20A	60	TCQYXM20A	160	TCQXXM20A	240				
21	TCQJXM21A	60	TCQYXM21A	160	TCQXXM21A	240				
22	TCQJXM22A	60	TCQYXM22A	160	TCQXXM22A	240				
23	TCQJXM23A	60	TCQYXM23A	160	TCQXXM23A	240				
24	TCQJXM24A	60	TCQYXM24A	160	TCQXXM24A	240	TCQZXM24A	375	TCQZXM24ADP	375
25	TCQJXM25A	60	TCQYXM25A	160	TCQXXM25A	240	TCQZXM25A	413		
26	TCQJXM26A	60	TCQYXM26A	160	TCQXXM26A	240	TCQZXM26A	448		
27	TCQJXM27A	60	TCQYXM27A	160	TCQXXM27A	240	TCQZXM27A	480	TCQZXM27ADP	480
29			TCQYXM29A	160	TCQXXM29A	240	TCQZXM29A	480		
30			TCQYXM30A	160	TCQXXM30A	240	TCQZXM30A	480	TCQZXM30ADP	480
32			TCQYXM32A	160	TCQXXM32A	240	TCQZXM32A	480	TCQZXM32ADP	480
34			TCQYXM34A	160	TCQXXM34A	240	TCQZXM34A	480	TCQZXM34ADP	480
36			TCQYXM36A	160	TCQXXM36A	240	TCQZXM36A	480	TCQZXM36ADP	480
41									TCQZXM41ADP	480
46									TCQZXM46ADP	480
50									TCQZXM50ADP	480
55									TCQZXM55ADP	480
60									TCQZXM60ADP	480

TORQUE TOOLS

HEADS

12 POINT RATCHET WRENCH HEADS - METRIC



Square Drive (mm)	J (0.425")	Max Torque Ft. Lbs.	Y (0.560")	Max Torque Ft. Lbs.
16	TCQJBOERM16	60		
18	TCQJBOERM18	60	TCQYBOERM18	160
22	TCQJBOERM22A	60		
24			TCQYBOERM24	160



TCQJBOERM18

12 POINT RATCHET WRENCH HEADS - SAE

Square Drive (Inches)	J (0.425")	Max Torque Ft. Lbs.	Y (0.560")	Max Torque Ft. Lbs.
3/8	TCQJBOER12	60		
7/16	TCQJBOER14	60		
1/2	TCQJBOER16	60		
9/16	TCQJBOER18	60	TCQYBOER18	112
5/8	TCQJBOER20	60	TCQYBOER20	160
11/16			TCQYBOER22	160
3/4	TCQJBOER24	60	TCQYBOER24	160



TCQJBOER14