



6 POINT FLARE NUT HEADS - METRIC



TCQJRXSM11A

Square Drive (mm)	J (0.425")	Max Torque Ft. Lbs.	Y (0.560")	Max Torque Ft. Lbs.
8	TCQJRXSM8A	17		
9	TCQJRXSM9A	25		
10	TCQJRXSM10A	33		
11	TCQJRXSM11A	42		
12	TCQJRXSM12A	50		
13	TCQJRXSM13A	58		
14	TCQJRXSM14A	60		
15	TCQJRXSM15A	60	TCQYRXSM15A	71
16	TCQJRXSM16A	60	TCQYRXSM16A	75
17	TCQJRXSM17A	60	TCQYRXSM17A	83
18	TCQJRXSM18A	60	TCQYRXSM18A	94
19	TCQJRXSM19A	60	TCQYRXSM19A	104
20	TCQJRXSM20A	60	TCQYRXSM20A	113
21			TCQYRXSM21A	113

6 POINT FLARE NUT HEADS - SAE



TCQJRXS8A

Square Drive (Inches)	J (0.425")	Max Torque Ft. Lbs.	Y (0.560")	Max Torque Ft. Lbs.
1/4	TCQJRXS8A	6		
5/16	TCQJRXS10A	17		
3/8	TCQJRXS12A	29		
7/16	TCQJRXS14A	42		
1/2	TCQJRXS16A	54		
9/16	TCQJRXS18A	60	TCQYRXS18A	74
5/8	TCQJRXS20A	60	TCQYRXS20A	74
11/16	TCQJRXS22A	60	TCQYRXS22A	92
3/4	TCQJRXS24A	60	TCQYRXS24A	104
13/16	TCQJRXS26A	60	TCQYRXS26A	117
7/8	TCQJRXS28A	60	TCQYRXS28A	133
15/16	TCQJRXS30A	60	TCQYRXS30A	146
1	TCQJRXS32A	60	TCQYRXS32A	158
1 1/8			TCQYRXS36A	160



RATCHETING FLARE NUT HEAD



TCRTWH40J

Square Drive (Inches)	J (0.425")	Y (0.560")	X (0.735")
9/16	TCRTWH36J		
5/8	TCRTWH40J		
11/16	TCRTWH44J		
3/4		TCRTWH48Y	
13/16	TCRTWH52J		
7/8		TCRTWH56Y	
15/16		TCRTWH60Y	
1		TCRTWH64Y	
1 1/8		TCRTWH72Y	
1 1/4		TCRTWH80Y	
1 3/8		TCRTWH88Y	
1 1/2			TCRTWH96X
16mm	TCRTWHM16J		
1 5/8		TCRTWH104Y	
1 7/8		TCRTWH120Y	

ADAPTORS



TCQZD32A-1

TCQZ-X

Product Code	Descriptions
TCQJ-Y	J Male to Y Female
TCQXY	X Male to Y Female
TCQY-X	Y Male to X Female
TCQZ-X	Z Male to X Female
TCQZD32A-1	Z Shank 1 Drive Ratchets



TORQUE TOOLS

HEADS