



NON-SPARKING SIDE CUTTING COMBINATION PLIERS

Copper Beryllium

Product Code	Overall Length	Jaw Width	Jaw Thickness
NSB400-160	6 ¼	1 9/16	3/8
NSB400-180	7	1	7/16
NSB400-200	8	1 1/8	1/2

Features

- Safe and suitable for use in hazardous environments to reduce the risk of producing ignitable sparks.
- Material: Copper Beryllium
- Anti-magnetic and highly corrosion resistant.



NSB400-180




NON-SPARKING DIAGONAL CUTTING PLIERS

Copper Beryllium

Product Code	Overall Length	Jaw Length	Cutting Edge Length
NSB402-160	6 ¼	6	7/8
NSB402-200	8	7 ¾	1 1/8
NSB403-160	6 ¼	6 ¼	7/8
NSB403-180	7	7 ¾	1 1/8

Features

- Safe and suitable for use in hazardous environments to reduce the risk of producing ignitable sparks.
- Material: Copper Beryllium
- NSB403 Series are Heavy Duty Pliers
- Anti-magnetic and highly corrosion resistant.



NSB402-160



NON-SPARKING FLAT NOSE PLIERS

Copper Beryllium

Product Code	Overall Length	Jaw Length
NSB404-160	6 ¼	1 1/2

Features

- Safe and suitable for use in hazardous environments to reduce the risk of producing ignitable sparks.
- Material: Copper Beryllium
- Anti-magnetic and highly corrosion resistant.



NSB404-160



NON-SPARKING ROUND NOSE PLIERS

Copper Beryllium

Product Code	Overall Length
NSB405-160	6 ¼

Features

- Safe and suitable for use in hazardous environments to reduce the risk of producing ignitable sparks.
- Material: Copper Beryllium
- Anti-magnetic and highly corrosion resistant.



NSB405-160