

ClickShare CSE-200+

Wireless collaboration solution for creative content-sharing
fit for enterprise roll-outs



- Up to 2 users on-screen
- Share from laptop, tablet or smartphone
- Smooth switching between wired and wireless sources
- Enhanced security features
- Annotation, blackboarding and touch back support on a 4K canvas
- Central management
- Delivered with 2 Buttons

Creativity boosts businesses. Enabling creative meetings, brainstorming and discussions enhance team collaboration and business outcomes. With the wireless collaboration solution, ClickShare, you bring effortless ideation and efficient collaboration in your enterprise.

Enriched sharing

The CSE-200+ offers interactive collaborative experiences for medium-sized meeting rooms. It allows up to 2 persons to share content simultaneously. Users simply plug a USB-powered device – the ClickShare Button – into their PC or Mac and click the button to get the content from their laptop on the large meeting room screen. With the ClickShare Apps, users can also share content from their laptops, mobile phones or tablets. Make sure to have the latest firmware installed on your Base Unit to enable the best experience with the Desktop App.

Stimulate creativity in your entire enterprise

The CSE-200+ was designed for enterprise rollouts. It offers a HDMI input for legacy equipment, easy switching between wireless and wired sources, enhanced security features, full network integration, a wide range of interactivity features - including annotation, blackboarding and touch back support on a 4K canvas and central management. Allowing up to 2 persons to share content simultaneously, the CSE-200+ encourages brainstorming and productivity in your enterprise.

The CSE-200+ is a product created with ISO 27001 certified flows and processes.

PRODUCT SPECIFICATIONS**CLICKSHARE CSE-200+**

General specifications	
Operating system	Windows 7/8/8.1/10 32 & 64 bit macOS 10.14/10.15 (Catalina) Android 9 & 10 (ClickShare app) iOS 11, 12 & 13 (ClickShare app)
Video outputs	1x HDMI 1.4b
Video inputs	1x HDMI 1.2
Output resolution	4K UHD (3840*2160) @ 30Hz
Input resolutions	1920x1080 @60Hz
Audio	Via HDMI, analog via Audio Jack 3.5mm, S/PDIF
AirPlay Support	iOS 11, 12 & 13 / macOS 10.14, 10.15
Google Cast Support	Android 9, 10
Miracast support	Miracast R2 support on Windows 10
Frame rate	Up to 30fps*
Number of sources simultaneous on screen	2
Number of simultaneous connections	16
iPad, iPhone and Android compatibility	Sharing of documents, browser, camera for both Android and iOS devices via ClickShare app
Extended desktop	Available for Windows, requires ClickShare Extension Pack.
Authentication protocol	WPA2-PSK in stand-alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/b/g/n/ac and IEEE 802.15.1
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels supported in select number of countries)
Connections	1x Ethernet LAN 1Gbit 1x USB Type-C 2.0 (back); 2x USB Type A 2.0 (back); 1x USB Type A 2.0 (front) Audio analog line out on mini jack socket (3.5mm), digital S/PDIF
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Warranty	3 years standard
*Note	*In optimal WiFi conditions with minimal WiFi interference and as measured during our quality validation. Check Network Deployment Guide for more info on WiFi optimisation and ideal configuration depending on your network environment.

ClickShare Base Unit dimensions	
Dimensions (HxWxD)	39mm x 200mm x 202mm
Power supply	Standard 110/220 V AC plug
Power consumption	Operational: 50W (max) Standby:
Weight	900 gr

Last updated: 13 Feb 2020Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.