

## 4K @ 60Hz High Speed HDMI 2.0 Cables - 3', 6', 15'

3D, Ethernet, ARC, HDR, 18Gbps, UL



HDMI3UL



HDMI6UL



HDMI15UL

SPECIFICATION	HDMI3UL	HDMI6UL	HDMI15UL
<b>Electrical Characteristics</b>			
Signal Bandwith	18Gbps		
Nominal Impedence with Tolerance	100Ω		
Nominal Compacitance	less 0.5pf		
Dielectric Strength	AC- 750V/1sec MIN		
Insulation Resistance	10MΩ		
Nominal Attenuation	300KHz		
<b>Physical Characteristics</b>			
Cable Bend Radius	75mm		
Package Type	Poly Bag		
<b>Conductor 1</b>			
Conductor Type	30AWG (1/0.254BC)		
Insulation	Foamed PE [0.65mm (White/Blue)]		
Drain Wire	30AWG (1/0.254BC)		
Shield	Aluminum Foil		
Braiding	16/4/0.12AL		
<b>Conductor 2</b>			
Conductor Type	30AWG (1/0.254BC)		
Insulation	HDPE 0.6mm		
<b>General</b>			
HDMI Cable Length	3'	6'	15'
Connector Type	19 Pin HDMI-A		
Plating	Gold		
Connector	PE (Inner Mould) / 45P PVC (Outer Mould)		
Jacket	Black PVC 6.0mm		
Approvals	ROHS/CE/UL		

Note: Specification subject to change without notice