IUI-AMAX-LCD8 LCD keypad, 8-zone

www.boschsecurity.com





- Single button arming of alarm system
- Fire, medical and panic alarms
- Tamper switch
- Stylish and modern design
- Backlight buttons for illuminated operation during day or night

The IUI-AMAX-LCD8 is an eight-zone LCD keypad, that is compatible with all AMAX panels. Easy to recognize icons display system conditions in a simple to view format. Zone status is indicated numerically across the top of the screen.

The codepad notifies you when a zone is open, when there has been an alarm, and in which zone the alarm has occurred.

Additionally there is a tamper contact included.

Functions

Arming methods

You can arm the system by entering your Code and pressing the [#AWAY] key, or quick arm the system by holding down the [#AWAY] key for 2 sec.

Fire, Medical and Panic alarms

If programmed to do so, simultaneously pressing the outside buttons of a row on any codepad triggers an audible alarm, and an alarm report is sent to the control panel. Press [4] and [6] simultaneously for a fire alarm; press [7] and [9] simultaneously for a medical alarm; and press [1] and [3] or [*STAY] and [#AWAY] simultaneously for a panic alarm.

Certifications and approvals

Region	Regulatory compliance/quality marks	
Germany	VdS	H 112001 AMAX panel 2000
Europe	CE	[IUI-AMAX-LCD8, IUI-AMAX-LED8]
	EN5013 1	EN-ST-000086 [AMAX Panel 2000 EN]

Quant Component	Parts included		
ity	Quant ity	Component	
1 LCD keypad	1	_CD keypad	

Technical specifications

Electrical

Minimum operating voltage in VDC	10.8
Maximum operating voltage in VDC	14.1
Minimum current consumption in mA	18

Standard current consumption in mA	75
Maximum current consumption in mA	100

Mechanical

Dimension in cm (H x W x D)	7.5 x 13.2 x 2.6
Dimension in inch (H x W x D)	3.0 x 5.2 x 1.0
Weight in g	138
Color	White
Cable type	four wire, unshielded and shielded 0.6 - 0.8 mm
Maximum cable length in m	150

Environmental

Minimum operating temperature in °C	-10
Maximum operating temperature in $^\circ\mathrm{C}$	55
Minimum relative humidity in %	10
Maximum relative humidity in %	95
Environmental class	Ш

Ordering information

IUI-AMAX-LCD8 LCD keypad, 8-zone AMAX keypad 2000 D8, 8 zones LCD icon keypad Order number IUI-AMAX-LCD8

Represented by:

Europe, Middle East, Africa: Europe, Middle Last, Africa Bosch Security Systems B.V. P.O. Box 80002 5600 JB Eindhoven, The Netherlands Phone: + 31 40 2577 284 emea.securitysystems@bosch.com emea.boschsecurity.com **Germany:** Bosch Sicherheitssysteme GmbH Robert-Bosch-Ring 5 85630 Grasbrunn Germany www.boschsecurity.com

North America: Bosch Security Systems, Inc. 130 Perinton Parkway Fairport, New York, 14450, USA Phone: +1 800 289 0096 Fax: +1 585 223 9180 onlinehelp@us.bosch.com www.boschsecurity.us

Asia-Pacific:

Asia-Pacific: Robert Bosch (SEA) Pte Ltd, Security Systems 11 Bishan Street 21 Singapore 573943 Phone: +65 6571 2808 Fax: +65 6571 2699 apr.securitysystems@bosch.com www.boschsecurity.asia

© Bosch Security Systems 2018 | Data subject to change without notice 5578106379 | en, V33, 24. Oct 2018