

Pressurized Closure System 2-Type 505 Endplate

The CORNING logo is a dark blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

Part Number:
80611038607

2-Type Endplates are offered in various diameters (up to 12.0 inches) and various cable entries (up to 3). Each assembly comes with sheath grip clamps. No drilling is needed in the field. The endplates are constructed from the same material as the closures and in the form of multiple sections for installation around uncut cables or existing splices. Only washer cutter tool and torque wrench is needed to install. Endplates come with the washers.

Pressurized Closure System 2-Type 505 Endplate



Specifications

General Specifications

Application	Aerial , Underground
Environment	Outdoor
Mounting Type	Aerial , Buried
Product Type	Splice Protection

Standards

Flame Retardance	No
------------------	----



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2020 Corning Optical Communications. All rights reserved.