

Closet Connector Housing (CCH) Module, pigtailed, SC Connectors Simplex, UPC, 12 F, Single-mode (OS2)



**Part Number:
CCH-RM12-3C-P03RH**

Corning closet connector housing (CCH) pigtail modules accommodate all industry-standard connector adapter types including the LC, ST® compatible, SC, SC duplex, FC and MT-RJ, as well as the keyed LC. Like LANscape® solutions panels, the modules are the same size for 6-, 8-, 12-, 16- and 24-fiber capacities. Each module provides strain-relief for the pigtail and offers the advantage of greater protection to the cables and connectors being installed when the pigtails will be routed and spliced in a separate housing. Available with both ribbon and 900 um tight-buffered MIC® cable types, each CCH module is factory terminated and tested. Each module is shipped assembled with adapters and connectorized pigtails installed to the customer's specifications.

Many of our fiber optic hardware products are highly configurable. If you don't see what you are looking for here, please review the ordering matrix contained in the family spec sheet found on the right, or contact Customer Care at 1-800-743-2675.



Features and Benefits

Factory-terminated and -tested

Guaranteed performance

Compatible with other LANscape® Solutions

System consistency

Strain-relief for pigtail

Fiber protection and reliability

Durable construction

Protection for connectors and adapters

Closest Connector Housing (CCH) Module, pigtailed, SC Connectors Simplex, UPC, 12 F, Single-mode (OS2)



Specifications

Design - Adapter	
Adapter Housing Color	Blue
Adapter Housing Material	Composite
Adapter Style	Standard
Adapter Type	SC
Insert Material	Ceramic

Design	
Fiber Count	12
Pigtail Length	3 m (9.84 ft)
Polish	UPC
Number of Adapters per Panel	12
Housing Type	Panels and Modules

General Specifications	
Fiber Category	Single-mode (OS2)
Cable type stubbed	MIC® Cable subunit
Product Type	Panels and Modules
Application	Data Center , Enterprise Networks

Optical Specification - Hardware	
Module Insertion Loss, Maximum (by 1310 nm)	0.4 dB

Closet Connector Housing (CCH) Module, pigtailed, SC Connectors Simplex, UPC, 12 F, Single-mode (OS2)



Optical Specification - Hardware

Module Insertion Loss, Typical (by 1310 nm)	0.15 dB
Module Insertion Loss, Maximum (by 1300 nm)	0.4 dB

Cable Design

Fiber Count	12
-------------	----

Connector Specs

Connector Type	SC
----------------	----

Specifications - Connector A

Polish	UPC
--------	-----

Ordering Information

Package Contents	CCH Module with 3 m pigtail; installation guide; two 1/8 x 4-in tie wraps, white; 3/16-in outer diameter Teflon spiral wrap, 10 ft
Units per Delivery	1/1

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Closet Connector Housing (CCH) Module, pigtailed, SC Connectors Simplex, UPC, 12 F, Single-mode (OS2)

The CORNING logo is displayed in white, uppercase letters within a solid blue rectangular box.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2020 Corning Optical Communications. All rights reserved.