

# FutureCom™ Metal Outlet, 4 ports, inclined, for 4 x LANscape® Jacks FutureCom™ Metal Outlet, 4 ports, inclined, for 4 x LANscape® Jacks

CORNING

**Part Number:  
WAXWSD-V0408-C001**

The 4-port LANscape® format industrial metal outlet with integrated cable strain relief can be equipped with copper jacks or fiber optic modules. It can be used for direct termination and, if used with additional splice tray (WAXLSD-00000-C001), it is also suitable for fusion splicing of fiber optic cables. The outlet is designed for harsh environment applications and can be wall-mounted as well as installed on Top-hat/DIN rails when used with a clip (clip attached).



# FutureCom™ Metal Outlet, 4 ports, inclined, for 4 x LANscape® Jacks FutureCom™ Metal Outlet, 4 ports, inclined, for 4 x LANscape® Jacks



## Specifications

### Environmental Conditions

Temperature Range, Installation -20 °C - 70 °C (-4 °F - 158 °F)

### Design

Color Anthracite

Number of Ports 4

### General Specifications

Halogen-free Yes

### Dimensions

Height 121 mm

Width 101 mm

Depth 79 mm

### Ordering Information

Weight 640 g

Units per Delivery 1/1

### Standards

RoHS Free of hazardous substances according to RoHS 2011/65/EU

**FutureCom™ Metal Outlet, 4 ports, inclined,  
for 4 x LANscape® Jacks FutureCom™ Metal  
Outlet, 4 ports, inclined, for 4 x LANscape®  
Jacks**

CORNING



Corning Optical Communications GmbH & Co. KG • Lelziger Strasse 121 • 10117 Berlin, Germany  
+00 800 2675 4641 • FAX: +49 30 5303 2335 • [www.corning.com/opcomm/emea](http://www.corning.com/opcomm/emea)