

Standard FutureCom™ Keystone Patch Panels 19" Standard FutureCom™ Keystone Patch Panels 19"



Part Number:
CAXXSV-02400-C001

The FutureCom™ patch panel is universally applicable for all 19" racks. This allows the free user-specific configuration of building and floor distributors.

The panel has a conductive front and integrated earthing or grounding points as well as two grounding lashes at the rear of the panel.

Features and Benefits

Universally applicable for all 19" rack

Suitable for all Keystone modules

Quick mount feature for easy one-person installation

Conductive front panel

Integrated cable strain relief

Two standardised grounding lashes for flat plugs

Integrated earthing points on the back side

Port numbering above and below ports

Space above ports can be used for customised labelling

Standard FutureCom™ Keystone Patch Panels 19" Standard FutureCom™ Keystone Patch Panels 19"

CORNING

Specifications

Environmental Conditions

Environmental Compatibility

Recyclable

Design

Number of Pieces

1

Housing Material

High-grade steel

Height Unit

1 U

Color

High-grade steel

Number of Ports

24

Mechanical Specifications

Cut Out

Keystone

Housing Material

High-grade steel

General Specifications

Product Category

Core Product

Environment

Indoor

Halogen-free

Yes

Dimensions

Height

152 mm

Width

43.6 mm

**Standard FutureCom™ Keystone Patch
Panels 19" Standard FutureCom™ Keystone
Patch Panels 19"**



Dimensions

Depth	483 mm
-------	--------

Ordering Information

Units per Delivery	1/1
--------------------	-----

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea