

Angled FutureCom™ LANscape Patch® Panels 19" Angled FutureCom™ LANscape Patch® Panels 19"

CORNING

Part Number: WAXWOV-04808-C001

The FutureCom™ angled patch panel is universally applicable for all 19-in racks and LAN-cabinets. This concept permits the free user-specific configuration of building and floor distributors. All LANscape module components can be built into LANscape cutouts which are planned for it. The angled patch panel 19-in 1U from the LANscape program is implemented in high-grade steel or black colored design. The patch panel is intended for fixed installation. It offers space for 24 pieces of single modules – FutureCom copper modules as well as FutureLink fiber optic modules. The front panel is electrically leading, integrated grounding points are available at the back. Likewise for grounding two latches are available for flat connectors. Particularly to emphasize is the simple and fast installation and clicking of the modules into the patch panel.



Features and Benefits

Suitable for all LANscape modules (FO and Copper)

Angled FutureCom™ LANscape Patch® Panels 19" Angled FutureCom™ LANscape Patch® Panels 19"



Specifications

Environmental Conditions

Environmental Compatibility	Recyclable
-----------------------------	------------

Design

Housing Material	Steel, RAL 9005
Height Unit	1.5 U
Color	Black
Number of Ports	48

Mechanical Specifications

Cut Out	LANscape®
Housing Material	Steel, RAL 9005

General Specifications

Environment	Indoor
-------------	--------

Dimensions

Height	224 mm
Width	44 mm
Depth	483 mm

Angled FutureCom™ LANscape Patch® Panels 19" Angled FutureCom™ LANscape Patch® Panels 19"



Ordering Information

Units per Delivery

1/1

Standards

RoHS Free of hazardous substances according to RoHS 2011/65/EU



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea