

Standard FutureCom™ LANscape® Patch Panels 19" Standard FutureCom™ LANscape® Patch Panels 19"



CORNING

Part Number: WAXWSV-04800-C002

The FutureCom™ patch panel is universally applicable for all 19-in racks and LAN-cabinets. This allows the free user-specific configuration of building and floor distributors. The front panel is electrically leading. Integrated grounding points are available at the back. Likewise for grounding 2 latches are available for flat connectors. Particularly to emphasize is the simple and fast installation and clicking of the modules into the patch panel.

Features and Benefits

Universally applicable for all 19" rack

Suitable for all LANscape modules (FO and Copper)

Quick mount feature for easy one-person installation

Conductive front panel

Integrated cable strain relief

Two standardised grounding lashes for flat plugs

Integrated earthing points on the back side

Port numbering above and below ports

Space above ports can be used for customised labelling

Standard FutureCom™ LANscape® Patch Panels 19" Standard FutureCom™ LANscape® Patch Panels 19"



Specifications

Environmental Conditions

Environmental Compatibility	Recyclable
-----------------------------	------------

Design

Housing Material	High-grade steel
Height Unit	1.5 U
Color	High-grade steel
Number of Ports	48

Mechanical Specifications

Cut Out	LANscape®
Housing Material	High-grade steel

General Specifications

Environment	Indoor
-------------	--------

Dimensions

Height	152 mm
Width	66 mm
Depth	483 mm

Standard FutureCom™ LANscape® Patch Panels 19" Standard FutureCom™ LANscape® Patch Panels 19"



Ordering Information

Units per Delivery

1/1

Standards

RoHS Free of hazardous substances according to RoHS 2011/65/EU



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea