ET-1080-R Vandal-resistant Speaker

www.boschsecurity.com





- ▶ 25 VRMS or 70 VRMS operation up to 8 W
- ► Low average current draw
- Extra protection and improved audibility through sealed-back speaker construction and vandal-resistant grill
- Compatible with SM and DSM Synchronization Modules
- ► Easy wiring with screw terminals

The Wheelock ET-1080-R Vandal-resistant Speaker meets the critical needs of the life safety industry for voice and tone signaling. It has a vandal-resistant die-cast grill and a sealed-back speaker for extra protection.

The high-efficiency speaker is designed for multiple power requirements with high dBA output at each power tap. It provides a choice of field-selectable taps from 0.125 W to 8 W across a frequency range of 400 Hz to 4 kHz for either 25 V and 75 V audio systems.

Certifications and approvals

Cooper Wheelock, Inc. holds these Listings and Approvals:

| Region | Certification | |
|--------|---------------|---|
| USA | UL | UEAY: Speakers (UL464), UUMW: Speakers and Amplifiers for Fire Protec- tive Signaling Systems (UL1480, UL1711, and UL2043) |
| | CSFM | see our website |

Installation/configuration notes

Compatible Products

The following products are compatible with the ET-1080 Speakers:

| Categor y | Product ID | Product Description |
|-------------------|-----------------------|-----------------------------------|
| Control Panels | D7022 ¹ | Conventional FACP |
| | D7024 ² | Addressable FACP |
| | D7024 | Conventional FACP |
| | D8024 ¹ | Analog FACP |
| | D9124 ¹ | Addressable FACP |
| | D10024A ¹ | Analog FACP |
| | FPD-7024 ² | Addressable FACP |
| | FPD-7024 | Conventional FACP |
| Modules | SM-12/24-R | Synchronization module (red) |
| | DSM-12/24-R | Dual synchronization module (red) |

These speakers are compatible with Wheelock SAFEPATH4 Facility Communication Systems and Bosch Voice Evacuation Systems.

2 | ET-1080-R Vandal-resistant Speaker

- ¹ For synchronization, use the SM or DSM modules with these control panels. The synchronization module must be set for 24 V operation. When used, the D7022 must be set for 24 VDC operation.
- ² When used with a D7039 Multiplex Expansion Module, the D7024 and FPD-7024 become addressable fire alarm control panels (FACPs).

Mounting

These speakers mount on the indicated back boxes for the indicated applications:

| | Conduit Applications | Surface Mounted | Flush Mounted |
|-------------------|-------------------------|--------------------|---------------|
| Four-inch square* | | | • |
| SBB Back Box | • | • | |

^{*} Requires an SER extension ring.

Wiring

The input terminals accept wires with diameters between 18 AWG and 12 AWG (ISO 0.75 mm² and 4 mm²).

Parts included

| Quant. | Component |
|--------|-----------------|
| 1 | Speaker |
| 1 | Hardware pack |
| 1 | Literature pack |

Technical specifications

Electrical

| Voltage (Input): | 24 VDC nominal; 16 VDC or FWR to 33 VDC or FWR |
|------------------|---|
|------------------|---|

Environmental

| Relative Humidity: | Up to 85%, non-condensing |
|--------------------------|-------------------------------|
| Temperature (Operating): | +32°F to +120°F (0° to +49°C) |

Mechanical

| Dimensions: | 4.375 in. square x 4.125 in. deep ¹ (11.1 cm square x 10.5 cm deep ¹) |
|-------------|--|
| Material: | Die-cast, high-impact plastic |

¹ When used in flush-mount installations, the unit extends 1.9375 in. (4.9 cm) from the mounting surface.

Speaker dB at 10 ft (3 m)

| 1/8 W | 78 dB |
|-------|-------|
| 1/4 W | 81 dB |
| 1/2 W | 84 dB |
| 1 W | 87 dB |

| 2 W | 89 dB |
|-----|-------|
| 4 W | 93 dB |
| 8 W | 96 dB |

Ordering information

ET-1080-R Vandal-resistant Speaker

The Wheelock ET-1080-R Vandal-resistant Speaker meets the critical needs of the life safety industry for voice and tone signaling. It has a vandal-resistant die-cast grill, a sealed-back speaker for extra protection, and is compatible with SM and DSM Synchronization Modules.

Order number ET-1080-R

Accessories

SBB-R Surface-mount Back Box (red)

14 cm (5.5 in.) x 14.2 cm (5.6 in.) x 9.1 cm (3.6 in.) Order number **SBB-R**

SFP-R Semi-flush Plate (red)

 $15.2~\mathrm{cm}$ (6 in.) square by $0.8~\mathrm{cm}$ ($0.3125~\mathrm{in.}$) thick Order number SFP-R

SSB-4 Ceiling Support Bridge

60.3 cm (23.75 in.) long by 16.5 cm (6.5 in.) wide Order number **SSB-4**

Represented by:

Americas:

Americas:
Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180 security.sales@us.bosch.com www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V. P.O. Box 80002 P.O. Box 80002 5617 BA Eindhoven, The Netherlands Phone: + 31 40 2577 284 Fax: +31 40 2577 330 emea.securitysystems@bosch.com www.boschsecurity.com

Asia-Pacific:

Asia-Pacific:
Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

China:
Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398 www.boschsecurity.com.cn

America Latina:

America Latina:
Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com