


**SCHLAGE** ■ **Briton**

Electronic Access  
Control Essentials



Backed by the strength of Allegion, Access control essentials features a variety of devices designed to fit the challenges of securing your facility. Whether it's commercial, industrial, banking, medical, retail or Hospitality. This portfolio includes a full range from electro-magnetic locks, power supplies and access control accessories.



### Electromagnetic locks

The broad portfolio of Schlage & Briton electromagnetic locks offer a solution for every application. Whether it's securing a hospital laboratory, monitoring a controlled area in an airport or providing traffic control for doors in an institutional building, Schlage & Briton magnetic door locks are designed to exceed the standards set by the Builders Hardware Manufacturers Association (BHMA). The portfolio encompasses a variety of hold force ratings, including 600 lbs. for traffic control & 1200 lbs. for high security.

### Power supplies

Power supplies and accessories offer enhanced flexibility and functionality specific to the changing needs of the access control market. They can be used in a variety of applications to convert high voltage AC power into the low voltage outputs required in most access control devices.

### System accessories

System accessories include a variety of devices that allow for specific functionality in stand alone applications or as part of networked access control. There are door contacts, emergency break glass & push buttons in this category.



3600U-DSM-MBS-L1

Electromagnetic Locks



## 3600U Electromagnetic Locks

Schlage introduces integrators an answer to their practical needs for electromagnetic locks. These compact electromagnetic locks are easy to stock, easy to select and easy to install. Schlage 3600U comes with 1200 lbs of holding force.

The Variety and flexibility of Schlage 3600U family electromagnetic locks can meet your demands for high security, traffic control, or narrow line applications throughout your facility.

All models are ideal for open architecture and easily interface with electronic access control systems, automatic door operators, and fire or other hazard sensing systems for egress and emergency egress.

## Benefits of using 3600U Electromagnetic Locks

- Field Selectable 12 or 24 VDC operation
- Simplified armature installation
- Variety of installation brackets available to adapt all kinds of environments
- Single magnet available with the 3600U Series
- UL294 and UL10C certification
- Tested to 500,000 Times life-cycle

# 3600U Electromagnetic Locks

## How to order 3600U

	3600U	- DSM	- MBS	- L1
Select model				
Select options/accessories				

### 1. Select Model

**3600U** High security, single lock

### 2. Select Options/Accessories

**DSM** Door status monitor

**MBS-L1** Magnetic bond sensor, with LED indicator for single door application

### Specifications

#### 3600U

<b>Holding force</b>	1200lbs.
<b>Input voltage</b>	12/24VDC field selectable
<b>Current draw</b>	0.5A@12VDC; 0.25A@24VDC.
<b>Dimension</b>	Lock body 268x73x40mm Armature plate 185x61x16mm Armature plate W/ DSM 252x61x16mm
<b>Weight</b>	10.75lbs.

**Anixter Part Number:** 10016724

## About Allegion

Allegion(NYSE: ALLE) is a global pioneer in seamless access, with leading brands like CISA®, Interflex®, LCN®, Schlage®, SimonsVoss® and Von Duprin®. Focusing on security around the door and adjacent areas, Allegion secures people and assets with a range of solutions for homes, businesses, schools and institutions. Allegion had \$2.7 billion in revenue in 2018, and sells products in almost 130 countries.

For more, visit [www.allegion.com/mea](http://www.allegion.com/mea)



© 2019 Allegion  
01/2020