


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	COLOR	UL LISTED * RATED LOAD lbs. (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/ 100 PIECES (g)
	MIN. in (mm)	MAX. in (mm)									
HLTP2I-X0	.25 (6.4)	1.91 (48.5)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	8.0 (203)	BLACK	40 (178)	INTERMEDIATE	.43 (196)
HLTP2I-X12	.25 (6.4)	1.91 (48.5)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	8.0 (203)	MAROON	40 (178)	INTERMEDIATE	.43 (196)
HLTP3I-X0	.25 (6.4)	3.18 (80.6)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	12.0 (305)	BLACK	40 (178)	INTERMEDIATE	.62 (282)
HLTP3I-X12	.25 (6.4)	3.18 (80.6)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	12.0 (305)	MAROON	40 (178)	INTERMEDIATE	.62 (282)

NOTES:

- 1) HLTP TIES ARE AVAILABLE IN BLACK AND MAROON ONLY.
- * 2) MINIMUM 2" (50.8 mm) OVERLAP REQUIRED TO ACHIEVE UL LISTED RATED LOAD. (1 IN² OR 645 mm²)
- 3) SUITABLE FOR USE IN AIR HANDLING SPACES PER NEC SEC. 300-22 (C) AND (D).
- 4) A MATERIAL SLUG MAY BE PRESENT AFTER MANUFACTURING. THE SLUG MAY REMAIN IN THE SLOT OR BE ON THE TIES.

PART NUMBER		SEE CHART	
TITLE			
TAK-TY HOOK & LOOP CABLE TIES HLTP SERIES FLAMMABILITY RATING: UL 94-V2 CUSTOMER DRAWING			
ITEM REVISION NAME		W10001CZ/07	
DATASET FILE NAME		W10001CZ/05-SS-27182	
		THIRD ANGLE PROJECTION	
MATERIAL		DRAWING NUMBER	
HOOKS: POLYPROPYLENE OR NYLON		SS-27182	
LOOPS: NYLON			
DRAWN BY	DATE	CHK	SCALE
KET	12/29/98	ENG	NONE
SHEET 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
07	1/3/20	JSP	DWW	ML	B. ADDED NOTE 4.	SS-27182
06	8/1/19	JSP	DWW	ML	A. REVISED MATERIAL	SS-27182