

# POWEREDGE R340

## Accelerate Business Growth

The Dell EMC PowerEdge R340 is a single-socket 1U rack server designed for productivity and data intensive applications for remote office/branch offices.



## Boost your business productivity

The Dell EMC PowerEdge R340 boosts business productivity, provides the flexibility to scale, and automates daily tasks. It is the ideal solution that allows you to focus on what matters: Accelerate your business growth. The R340 offers features to support your demanding and growing business needs.

- Accelerate your business with improved performance due to 100% more cores with Intel® Xeon® E-2200 processors, 11% increase in memory speed, and 20% more PCIe lanes.<sup>1</sup>
- Harness data growth with up to 8 x internal 2.5" or 4 x 3.5" hot-plug hard drives.
- Manage operational costs with Multi-Vector cooling which automatically calculates and delivers the proper airflow needed for optimal cooling.

## Simplify your IT infrastructure

The Dell OpenManage portfolio offers innovations that simplifies management tasks, making IT operations efficient and cost-effective throughout the server lifecycle.

- The embedded iDRAC9 with Lifecycle Controller, server deployment, configuration and updates are fast and worry-free.
- Access your servers anywhere, anytime from your mobile device with OpenManage Mobile (requires OpenManage Enterprise).
- Resolve issues with up to 72% less IT effort using automated proactive and predictive technology from ProSupport Plus and SupportAssist.<sup>2</sup>

## Keep your data safe

Every PowerEdge server is made with a cyber-resilient architecture, building security into the server's entire life cycle. Dell EMC is laser-focused on security (from design to end-of-life) to ensure trust and deliver worry-free, secure servers.

- Keep your data safe with software RAID.
- Maintain data safety with cryptographically-signed firmware packages and Secure Boot.
- Protect your server from malicious malware with iDRAC9 Enterprise Server Lockdown mode.
- Wipe all data from storage media quickly and securely with System Erase

### PowerEdge R340

- Improved performance due to 100% more cores
- Scale with 17% more storage capacity
- Protect your server from malicious malware with iDRAC9 Enterprise Server Lockdown mode

<sup>1</sup> Based on Dell EMC Internal analysis comparing R340 vs the previous generation. September 2019.

<sup>2</sup> Based on June 2018 Principled Technologies Report commissioned by Dell EMC, "Save time and IT effort resolving server hardware issues with ProSupport Plus and SupportAssist", compared to Basic Warranty without SupportAssist.

# PowerEdge R340

Features	Technical Specification	
Processor	1 processor from the following: Intel® Xeon® E-2200 product family, Intel Pentium®, Intel Core i3®, Intel Celeron®	
Memory	4 x DDR4 DIMM slots, Supports UDIMM, up to 2666MT/s, 64GB Max. Supports registered ECC	
Storage controllers	Internal controllers: PERC H730P, H330, HBA330 Software RAID: PERC S140 External controllers: 12Gbps SAS HBA	
Internal boot	Boot Optimized Storage Subsystem (BOSS): 2 x M.2 240GB (RAID 1 or No RAID) or 1 x M.2 240GB (No RAID only) Internal Dual SD Module <sup>3</sup> : 2x microSD (16GB, 32GB or 64GB) or 1x microSD (16GB, 32GB or 64GB)	
Drive bays	Up to 8 x 2.5 hot-plug SATA, SAS (optional) or SSD Up to 4 x 3.5 hot-plug SATA, SAS (optional) or SSD	
Power supplies	Single or dual 350W (Platinum) or 550W (Platinum) hot-plug redundant power supplies	
Dimensions	Form factor: Rack (1U)	Chassis width: 434.00mm (17.08 in) Chassis depth: 595.63mm (23.45 in) (3.5" HDD config) Chassis depth: 544.836mm (21.45 in) (2.5" HDD config) Note: These dimensions do not include: bezel, redundant PSU Chassis weight: 13.6 kg (29.98 lb.)
Embedded management	iDRAC9 with Lifecycle Controller iDRAC Direct iDRAC RESTful API with Redfish	
Bezel	Optional security bezel	
OpenManage™ Software	OpenManage Enterprise	OpenManage Power Manager OpenManage Mobile
Integrations and connections	Integrations: Microsoft® System Center VMware® vCenter™ BMC Truesight (available from BMC) Red Hat Ansible	Connections: Nagios Core & Nagios XI Micro Focus Operations Manager i (OMi) IBM Tivoli Netcool/OMNIBus
Tools	iDRAC Service Module OpenManage Server Administrator Dell EMC Repository Manager Dell EMC System Update	Dell EMC Server Update Utility Dell EMC Update Catalogs Dell EMC RACADM CLI IPMI Tool
Security	TPM 1.2/2.0 optional Cryptographically signed firmware Silicon Root of Trust	Secure Boot System Lockdown (requires OpenManage Enterprise) System Erase
I/O & Ports	Networking Options: 2 x 1GbE LOM Network Interface Controller (NIC) ports Front ports: 1x USB 2.0, 1 x iDRAC micro USB 2.0 management port Rear ports: 2 x USB 3.0, VGA, serial connector	2 x PCIe Gen 3.0 slots: • One x8 slot low-profile, half-length with x4 slot width • One x16 slot low-profile/full-height, half-length with x8 bandwidth
Supported operating systems	Citrix® XenServer® Microsoft® Windows Server® with Hyper-V (2016 and 2019) Red Hat® Enterprise Linux Ubuntu® Server LTS	SUSE® Linux Enterprise Server VMware® ESXi For specifications and interoperability details, see <a href="https://www.dell.com/OSsupport">Dell.com/OSsupport</a> .
OEM-ready version available	From bezel to BIOS to packaging, your servers can look and feel as if they were designed and built by you. For more information, visit <a href="https://www.dell.com/OEM">Dell.com/OEM</a> .	
Recommended support	ProSupport Plus for critical systems or ProSupport for comprehensive hardware and software support for your PowerEdge solution. Consulting and deployment offerings are also available. Contact your Dell EMC representative today for more information. Availability and terms of Dell EMC Services vary by region. For more information, visit <a href="https://www.dell.com/ServiceDescriptions">Dell.com/ServiceDescriptions</a> .	
Dell Financial Services	Deliver results with easy financing. Explore financial options that move at the speed of business. For more information, visit <a href="https://www.emc.com/products/how-to-buy/global-financial-services/index.htm">https://www.emc.com/products/how-to-buy/global-financial-services/index.htm</a> .*	

3 ESXi (only OS supported)

Learn more at [DellEMC.com/PowerEdge](https://www.dell.com/PowerEdge)

## End-to-end technology solutions

Reduce IT complexity, lower costs and eliminate inefficiencies by making IT and business solutions work harder for you. You can count on Dell for end-to-end solutions to maximize your performance and uptime. A proven leader in Servers, Storage and Networking, Dell Enterprise Solutions and Services deliver innovation at any scale. And if you're looking to preserve cash or increase operational efficiency, Dell Financial Services™ has a wide range of options to make technology acquisition easy and affordable. Contact your Dell Sales Representative for more information.\*\*

©2019 Dell Inc. All rights reserved. Dell, the DELL logo, the DELL badge, PowerEdge, and OpenManage are trademarks of Dell Inc. Other trademarks and tradenames may be used in this document to refer to either the entities claiming the marks and names or their products. Dell disclaims proprietary interest in the marks and names of others. This document is for informational purposes only. Dell reserves the right to make changes without further notice to any products herein. The content provided is as is and without express or implied warranties of any kind. \*\*Leasing and financing provided and serviced by Dell Financial Services L.L.C. or its affiliate or designee ("DFS") for qualified customers. Offers may not be available or may vary in certain countries. Where available, offers may be changed without notice and are subject to product availability, credit approval, execution of documentation provided by and acceptable to DFS, and may be subject to minimum transaction size. Offers not available for personal, family or household use. Dell and the DELL logo are trademarks of Dell Inc. ( may be a newer version)

Copyright © December 2019 Dell Inc. or its subsidiaries. All Rights Reserved.

