

## Cat6a 10G-Certified Snagless Shielded STP Ethernet Cable (RJ45 M/M), PoE, Gray, 8 ft.

MODEL NUMBER: N262-008-GY



Snagless Cat6a cable with Power over Ethernet (PoE) connects 10G equipment in your high-speed 10GBase-T network.

### Features

#### High-Speed Cat6a STP Patch Cable Ideal for Your 10GBase-T Ethernet Network

Designed for fast transmission and excellent signal quality, this eight-foot Cat6a cable ensures peak performance throughout your local area network (LAN). It transmits 10 Gbps data, voice and video through high-speed 10G equipment, including network switches, modems, routers, adapters, hubs and patch panels. At 500 MHz, it reduces impedance and structural return loss compared to standard 100 MHz wire.

#### Supports Power over Ethernet to Save You Money and Give You More Installation Choices

Because this Cat6a shielded cable supports PoE, it can supply the power to operate compatible PoE devices, such as security cameras, VoIP telephones, point-of-sale kiosks and access control devices. This saves you the expense and effort of purchasing, connecting and installing individual power supplies for each device. It also helps you install PoE devices in areas far away from AC outlets, such as poles or ceilings.

#### Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. The N262-008-GY shields against disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

#### Snagless RJ45 Male Connectors Add Extra Protection During Installation

The RJ45 connectors' snagless design protects the locking tabs from being damaged or broken off during installation. The ends are shielded to minimize near-end crosstalk (NEXT) levels. Integral strain relief gives the N262-008-GY extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

### Highlights

- Cat6a STP patch cord rated for high-speed 10 Gbps communications
- Ideal for connecting 10G network switches, routers, hubs and other equipment
- Supports PoE to save you expense and effort of powering PoE devices individually
- Disperses EMI/RFI line noise that can destroy data and affect equipment performance
- Snagless RJ45 connectors prevent tabs from being damaged during installation

### Applications

- Connect 10GBase-T networks or digital signage in a high-density data center
- Deliver power to PoE devices mounted in areas that are difficult to reach or have no electrical outlets
- Replace an old or missing RJ45 cable
- Provide universal connectivity for LAN network components, such as switches, servers, modems, routers, adapters, VoIP phones, security cameras and point-of-sale kiosks

### Package Includes

- N262-008-GY Cat6a 10G-Certified Snagless Shielded STP Ethernet Cable (RJ45 M/M), Gray, 8 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

## Specifications

| OVERVIEW                    |                              |
|-----------------------------|------------------------------|
| UPC Code                    | 037332256751                 |
| INPUT                       |                              |
| Cable Length (ft.)          | 8                            |
| Cable Length (m)            | 2.4                          |
| Cable Length (in.)          | 96                           |
| PHYSICAL                    |                              |
| Cable Jacket Rating         | CM                           |
| Cable Outer Diameter (OD)   | 6.2mm                        |
| Cable Shielding             | STP                          |
| Color                       | Gray                         |
| Material of Construction    | PVC                          |
| Snagless Connector          | Yes                          |
| Wire Gauge (AWG)            | 26                           |
| Wire Type                   | Stranded                     |
| ENVIRONMENTAL               |                              |
| Operating Temperature Range | 14 to 122 F (-10 to 50 C)    |
| Storage Temperature Range   | 5 to 140 F (-15 to 60 C)     |
| Operating Humidity Range    | 0% to 90% RH, Non-Condensing |
| Storage Humidity Range      | 0% to 90% RH, Non-Condensing |
| COMMUNICATIONS              |                              |
| Network Speed               | 10Gbps                       |
| IEEE Standards Supported    | 802.3at                      |
| CONNECTIONS                 |                              |
| Side A - Connector 1        | RJ45 (MALE)                  |
| Side B - Connector 1        | RJ45 (MALE)                  |
| Contact Plating             | Gold                         |
| FEATURES & SPECIFICATIONS   |                              |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                        |                           |
|----------------------------------------|---------------------------|
| Technology                             | Cat6a                     |
| <b>STANDARDS &amp; COMPLIANCE</b>      |                           |
| Certifications                         | RoHS, REACH               |
| <b>WARRANTY</b>                        |                           |
| Product Warranty Period<br>(Worldwide) | Lifetime limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>