


Cat8 25G/40G-Certified Snagless Shielded S/FTP Network Ethernet Cable (RJ45 M/M), PoE, White, 40 ft.

MODEL NUMBER: **N272-040-WH**



Shielded Cat8 cable connects 25G/40G equipment in your top-of-the-line 40GBase-T data center.

Features

High-Speed Cat8 S/FTP Ethernet Cable Up to 4 Times Faster Than Cat6a

This certified Cat8 cable transmits 40 Gbps data, voice and audio/video through high-speed 40G equipment, such as high-speed switch-to-switch communication devices in your data center. Not only is its 40 Gbps data transfer speed four times that of Cat6a cable, but this Cat8 cable also supports bandwidth up to 2 GHz (2000 MHz) for carrying information and streaming video with no lag.

Supports Power over Ethernet (PoE) to Cut Down on Power Supplies

Because this Cat8 shielded cable supports PoE, it can supply the power to operate compatible PoE devices, including network switches, security cameras, equipment sensors and wireless access points. This saves you the expense and effort of purchasing, connecting and installing individual power supplies for each device. You can also install PoE devices in locations distant from power outlets, such as high on walls, ceilings or poles.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

EMI (electromagnetic interference) and RFI (radio frequency interference) line noise is a common cause of performance problems. The 22 AWG S/FTP (shielded foiled twisted pair) cable's foil shielding blocks disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer. Near-end crosstalk (NEXT) levels are practically eliminated, so you don't have to worry about keeping your cables separated in crowded pathways or spend valuable time on field testing.

Snagless RJ45 Male Connectors Add Extra Protection During Installation

The RJ45 connectors' snagless design protects the locking tabs from being damaged or broken off during installation. Integral strain relief provides extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

White Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

This Cat8 Ethernet cable features a durable white PVC jacket, which allows easy, fast identification in a crowded rack, patch panel or workstation and helps prevent the cable from becoming accidentally disconnected.

Highlights

- Certified Cat8 S/FTP Ethernet cord rated for 40 Gbps networks—4x faster than Cat6a
- Supports PoE to save you expense and effort of powering PoE devices individually
- Disperses EMI/RFI line noise that can destroy data and affect equipment performance
- Snagless RJ45 connectors prevent tabs from being damaged during installation
- White PVC jacket allows fast, easy identification in a crowded rack or workstation

Applications

- Connect 40GBase-T networks or digital signage in your office, school or retail business' high-density server room or data center
- Deliver power to PoE devices, including network switches, security cameras and wireless access points, mounted in areas that are difficult to reach or have no electrical outlets

Package Includes

- N272-040-WH Cat8 25G/40G-Certified Snagless Shielded Ethernet Cable (RJ45 M/M), White, 40 ft.



Specifications

OVERVIEW	
UPC Code	037332256379
INPUT	
Cable Length (ft.)	40
Cable Length (m)	12.2
Cable Length (in.)	480
PHYSICAL	
Cable Jacket Rating	CM
Cable Outer Diameter (OD)	8.0mm
Cable Shielding	S/FTP
Color	White
Crossover Wiring	No
Material of Construction	PVC
Snagless Connector	Yes
Wire Gauge (AWG)	22
Wire Type	Solid
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	-5 to 140 F (-15 to 60 C)
Operating Humidity Range	0% TO 90% RH, NON-CONDENSING
Storage Humidity Range	0% TO 90% RH, NON-CONDENSING
COMMUNICATIONS	
Network Speed	40 Gbps
IEEE Standards Supported	802.3bt
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Contact Plating	Gold
FEATURES & SPECIFICATIONS	



Technology	PoE; Cat8
STANDARDS & COMPLIANCE	
Certifications	RoHs, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>