

SKINDICHT® SM-PE/SM-PE-M

Nickel-plated brass grounding locknuts for PG & metric strain relief cable glands



SKINDICHT® SM-PE locknuts are required wherever varnished, anodized, and powder-coated housings are used. When the locknut is tightened, the raised edges cut through the insulating layer, guaranteeing optimum contact. Ideal for use with SKINTOP® MS-SC or SKINTOP® BRUSH grounding cable glands.

Approvals**Technical data**

 **Material:** nickel-plated brass

 **Temperature range:** -20°C to +100°C

PG

Part number	Size	Wrenching flats	Nut thickness in	Pack size
52103200	PG 7	0.591	0.185	100
52103210	PG 9	0.709	0.185	100
52103220	PG 11	0.827	0.185	100
52103230	PG 13	0.906	0.185	100
52103240	PG 16	1.024	0.185	100
52103250	PG 21	1.260	0.204	50
52103260	PG 29	1.615	0.224	50
52103270	PG 36	2.009	0.263	50

metric

Part number	Size	Wrenching flats	Nut thickness in	Pack size
52103300	M12 x 1.5	0.591	0.137	100
52103310	M16 x 1.5	0.748	0.137	100
52103320	M20 x 1.5	0.945	0.145	100
52103330	M25 x 1.5	1.182	0.165	50
52103340	M32 x 1.5	1.418	0.185	50
52103350	M40 x 1.5	1.812	0.216	25
52103360	M50 x 1.5	2.364	0.216	10
52103370	M63 x 1.5	2.758	0.275	10
52103371	M75 x 1.5	3.349	0.315	5
52103372	M90 x 2.0	4.018	0.394	1
52103373	M110 x 2.0	4.885	0.472	1