

## SKINTOP® SD

Dust- &amp; moisture-proof plugs for NPT, PG &amp; metric strain relief cable glands



SKINTOP® SD is designed for use when a SKINTOP® cable gland is installed without a cable. The plugs prevent dust and dirt from entering the housing interior until final cable installation is completed.

## ■ Technical data

Material: PE foam

## ■ Approvals



| Part number | PG    | SKINTOP® size |               |            | Diameter |      | Thickness |    | Pack size |
|-------------|-------|---------------|---------------|------------|----------|------|-----------|----|-----------|
|             |       | metric        | polyamide NPT | metal NPT  | in       | mm   | in        | mm |           |
| 52025235    | PG 7  | —             | —             | —          | 0.413    | 10.5 | 0.078     | 2  | 500       |
| 52025240    | PG 9  | —             | NPT 3/8"      | —          | 0.531    | 13.5 | 0.078     | 2  | 500       |
| 52025250    | PG 11 | —             | —             | —          | 0.669    | 17.0 | 0.078     | 2  | 250       |
| 52025260    | PG 13 | —             | NPT 1/2"      | —          | 0.728    | 18.5 | 0.078     | 2  | 250       |
| 52025270    | PG 16 | —             | —             | —          | 0.807    | 20.5 | 0.078     | 2  | 250       |
| 52025280    | PG 21 | —             | NPT 3/4"      | —          | 1.024    | 26.0 | 0.078     | 2  | 100       |
| 52025290    | PG 29 | —             | NPT 1"        | —          | 1.359    | 34.5 | 0.078     | 2  | 100       |
| 52025291    | PG 36 | —             | —             | —          | 1.753    | 44.5 | 0.078     | 2  | 100       |
| 54113100    | —     | M12           | —             | NPT 1/4"   | 0.453    | 11.5 | 0.078     | 2  | 100       |
| 54113110    | —     | M16           | —             | NPT 3/8"   | 0.591    | 15.0 | 0.078     | 2  | 100       |
| 54113120    | —     | M20           | —             | NPT 1/2"   | 0.788    | 20.0 | 0.078     | 2  | 100       |
| 54113130    | —     | M25           | —             | NPT 3/4"   | 0.985    | 25.0 | 0.078     | 2  | 50        |
| 54113140    | —     | M32           | —             | NPT 1"     | 1.182    | 30.0 | 0.078     | 2  | 50        |
| 54113150    | —     | M40           | —             | NPT 1 1/4" | 1.576    | 40.0 | 0.078     | 2  | 25        |
| 54113160    | —     | M50           | —             | NPT 1 1/2" | 1.930    | 49.0 | 0.078     | 2  | 25        |
| 54113170    | —     | M63           | —             | NPT 2"     | 2.285    | 58.0 | 0.078     | 2  | 25        |

## SKINTOP® DV

Dust- &amp; moisture-proof plugs for NPT, PG &amp; metric strain relief cable glands



SKINTOP® DV is designed for use when a SKINTOP® cable gland is installed without a cable. They prevent dust, dirt, and moisture from entering the housing interior until final cable installation is completed.

## ■ Technical data

Material: CR

## ■ Approvals



| Part number | PG    | SKINTOP® size |               |            | Diameter |      | Thickness |      | Pack size |
|-------------|-------|---------------|---------------|------------|----------|------|-----------|------|-----------|
|             |       | metric        | polyamide NPT | metal NPT  | in       | mm   | in        | mm   |           |
| 53800640    | PG 7  | —             | —             | —          | 0.275    | 7.0  | 0.256     | 6.5  | 500       |
| 53800641    | PG 9  | —             | NPT 3/8"      | —          | 0.334    | 8.5  | 0.295     | 7.5  | 500       |
| 53800579    | PG 11 | —             | —             | —          | 0.413    | 10.5 | 0.334     | 8.5  | 250       |
| 53800583    | PG 13 | —             | NPT 1/2"      | —          | 0.492    | 12.5 | 0.334     | 8.5  | 250       |
| 53800642    | PG 16 | —             | —             | —          | 0.571    | 14.5 | 0.354     | 9.0  | 250       |
| 53800643    | PG 21 | —             | NPT 3/4"      | —          | 0.728    | 18.5 | 0.433     | 11.0 | 100       |
| 54113000    | —     | M12           | —             | NPT 1/4"   | 0.283    | 7.2  | 0.275     | 7.0  | 500       |
| 54113010    | —     | M16           | —             | NPT 3/8"   | 0.394    | 10.0 | 0.315     | 8.0  | 500       |
| 54113020    | —     | M20           | —             | NPT 1/2"   | 0.520    | 13.2 | 0.330     | 8.4  | 250       |
| 54113030    | —     | M25           | —             | NPT 3/4"   | 0.677    | 17.2 | 0.374     | 9.5  | 250       |
| 54113040    | —     | M32           | —             | NPT 1"     | 0.835    | 21.2 | 0.472     | 12.0 | 250       |
| 54113050    | —     | M40           | —             | NPT 1 1/4" | 1.111    | 28.2 | 0.571     | 14.5 | 100       |
| 54113060    | —     | M50           | —             | NPT 1 1/2" | 1.410    | 35.8 | 0.709     | 18.0 | 100       |
| 54113070    | —     | M63           | —             | NPT 2"     | 1.796    | 45.6 | 0.788     | 20.0 | 50        |