

PG → NPT adapters



Part number	Size		Pack size
	male	→ female	
01112	PG 11	→ NPT 1/2"	10
01312	PG 13	→ NPT 1/2"	10
01612	PG 16	→ NPT 1/2"	10
02112	PG 21	→ NPT 1/2"	10
02134	PG 21	→ NPT 3/4"	10
02910	PG 29	→ NPT 1"	10
03614	PG 36	→ NPT 1 1/4"	10

■ Approvals



NPT → PG adapters



Part number	Size		Pack size
	male	→ female	
11211	NPT 1/2"	→ PG 11	10
11213	NPT 1/2"	→ PG 13	10
11216	NPT 1/2"	→ PG 16	10
13411	NPT 3/4"	→ PG 11	10
13413	NPT 3/4"	→ PG 13	10
13416	NPT 3/4"	→ PG 16	10
13421	NPT 3/4"	→ PG 21	10
11116	NPT 1"	→ PG 16	10

■ Approvals



SKINDICHT® MA-M metric → NPT adapters



Part number	Size*		Pack size
	male	→ female	
54020100	M16	→ NPT 1/2"	50
54020110	M20	→ NPT 1/2"	50
54020120	M25	→ NPT 1/2"	25
54020130	M25	→ NPT 3/4"	25
54020140	M32	→ NPT 1/2"	25
54020152	M32	→ NPT 1"	25
54020153	M40	→ NPT 1 1/4"	10

* Thread pitch is 1.5 mm

■ Approvals



SKINDICHT® MA-M metric → PG adapters



Part number	Size*		Pack size
	male	→ female	
52104200	M16	→ PG 7	100
52104210	M20	→ PG 9	50
52104220	M25	→ PG 11	50
52104230	M25	→ PG 13	50
52104240	M25	→ PG 16	50
52104250	M32	→ PG 16	25

* Thread pitch is 1.5 mm

Part number	Size*		Pack size
	male	→ female	
52104260	M32	→ PG 21	25
52104270	M40	→ PG 21	25
52104280	M50	→ PG 29	10
52104290	M63	→ PG 36	10
52104300	M63	→ PG 42	10

■ Approvals



SKINDICHT® ZS-M metric → PG adapters



Part number	Size*		Pack size
	male	→ female	
52104330	M12	→ PG 7	100
52104340	M16	→ PG 9	100
52104010	M16	→ PG 11	100
52104360	M20	→ PG 11	100
52104370	M20	→ PG 16	100
52104380	M20	→ PG 16	50

* Thread pitch is 1.5 mm

Part number	Size*		Pack size
	male	→ female	
52104400	M25	→ PG 21	50
52104410	M32	→ PG 29	25
52104420	M40	→ PG 36	10
52104430	M50	→ PG 42	10
52104440	M63	→ PG 48	10

■ Approvals



SKINDICHT® MA-PG → metric adapters

shape A



shape B



■ Technical data

Material: nickel-plated brass

■ Approvals



shape A

Part number	Size*		Pack size
	male	→ female	
52104492	PG 11	→ M16	50
52104495	PG 16	→ M20	50
52104497	PG 21	→ M20	50
52104498	PG 21	→ M25	50
52104500	PG 29	→ M25	25
52104501	PG 29	→ M32	25
52104503	PG 36	→ M40	10

shape B

Part number	Size*		Pack size
	male	→ female	
52104490	PG 7	→ M12	100
52104491	PG 9	→ M16	50
52104493	PG 11	→ M20	50
52104494	PG 13	→ M20	50
52104496	PG 16	→ M25	50
52104499	PG 21	→ M32	50
52104502	PG 29	→ M40	10

* Thread pitch is 1.5 mm

SKINDICHT® A-PG → metric adapters

shape A



shape B



■ Technical data

Material: glass fiber reinforced polyamide

Temperature range: -40°C to +100°C

Color: light gray (RAL 7035)

■ Approvals



Part number		Size*		Pack size
shape A	shape B	male	→ female	
52100320	—	PG 7	→ M12	25
52100321	—	PG 7	→ M16	25
52100322	—	PG 9	→ M12	25
52100323	—	PG 9	→ M16	25
52100324	—	PG 9	→ M20	25
52100325	—	PG 11	→ M16	25
52100326	—	PG 11	→ M20	25
52100327	—	PG 11	→ M25	25
52100328	—	PG 13	→ M16	25
52100329	—	PG 13	→ M20	25
52100330	—	PG 13	→ M25	25
52100331	—	PG 16	→ M20	25
52100332	—	PG 16	→ M25	25
52100333	—	PG 16	→ M32	25
52100334	—	PG 21	→ M25	10
52100335	—	PG 21	→ M32	10
52100336	—	PG 21	→ M40	10
—	52100337	PG 29	→ M32	10
52100338	—	PG 29	→ M40	10
52100339	—	PG 29	→ M50	10
—	52100340	PG 36	→ M40	10
52100341	—	PG 36	→ M50	10
52100342	—	PG 36	→ M63	10
—	52100343	PG 42	→ M40	5
52100344	—	PG 42	→ M50	5
52100345	—	PG 42	→ M63	5
—	52100346	PG 48	→ M50	5
52100347	—	PG 48	→ M63	5

* Thread pitch is 1.5 mm