

SKINMATIC® RZ wrench



The SKINMATIC® RZ tool is designed for fast assembly of cable glands. The wrench has two expandable clamping ranges (lock positions) and fits SKINTOP® sizes PG 7 - 21, NPT 3/8" - NPT 3/4", and M12 - M25. This tool provides access to SKINTOP® glands in cramped conditions and is ideal for OEM installations.

Part number	Width across flats in	Height in	Length in	Pack size
61791260	0.55 - 1.30	3.150	9.843	1

SKINMATIC® MH-Set

Mounting tools for SKINTOP® brass products



MH-Set is a three piece wrench set intended for use with SKINTOP® MS products such as MS-M, MS-SC-M, and MS-NPT. The bearing surface is shaped to prevent the nut from slipping and ensures a quick and safe assembly. The MH-Set includes the following sizes:

- 16/20 mm (M12/M16)
- 24/29 mm (M20/M25)
- 36/45 mm (M32/M40)

Part number	Size	Wrench size		Thickness	
		in	mm	in	mm
61791273	M12/M16	0.630 - 0.788	16 - 20	7.88	200
	M20/M25	0.945 - 1.142	24 - 29	8.66	220
	M32/M40	1.418 - 1.773	36 - 45	9.85	250

PTS4 wire stripper



The PTS4 is designed for stripping single conductors from 0.25 mm² (24 AWG) to 4 mm² (12 AWG). It can be used to strip several conductors of the same gauge size simultaneously. The blades are self-adjusting to prevent damage to the conductors. In addition, the pressure of the cutting jaw may be adjusted. Diagonal cutters are also integrated so that cutting and stripping can be done with the same tool.

Part number	Description	Length in	Weight lbs	Pack size
61725950	PTS4	6.698	0.441	1
61753620	spare spring	—	—	1

BULLI cable shears



The BULLI cutters are special designed for use with fine wire cables up to 16 mm² (6 AWG). It features a latch and spring return, along with a safety lock for extra protection.

Part number	Description	For outer diameter	Length in	Weight lbs	Pack size
61744160	shears	0.630	7.289	0.298	1
61744161	spare spring	—	—	—	1

KS 15 cable shears



Cuts copper and aluminum cables with an outer diameters of up to 15 mm (0.59 in). The KS 15 provides easy, precision cutting that can be used for removing the jacket and stripping wires. Not suitable for steel wire and hard-drawn copper conductors.

Part number	For outer diameter in	Length in	Weight lbs	Pack size
61735975	0.591	6.501	0.463	1

SKINMATIC® KB-M

Multi-purpose tap



For simultaneous core drilling and cutting of metric threads. Especially suitable for thin components and sheet metals.

Part number	Size	Overall length		Drill length		Pack size
		in	mm	in	mm	
61791274	M12 x 1.5	5.12	130	1.18	30	1
61791275	M16 x 1.5	5.91	150	1.38	35	1
61791276	M20 x 1.5	6.50	165	1.57	40	1
61791277	M25 x 1.5	7.28	185	1.77	45	1

SKINDICHT® SB-M

Spiral drill



For drilling the core holes of metric threads.

Part number	Size	Overall length		Drill length		Pack size
		in	mm	in	mm	
61791278	M32 x 1.5	11.85	301	7.09	180	1
61791279	M40 x 1.5	13.75	349	7.88	200	1
61791280	M50 x 1.5	14.53	369	8.66	220	1

SKINDICHT® GB-M

Thread cutting bit



For cutting metric threads.

Part number	Size	Overall length		Drill length		Pack size
		in	mm	in	mm	
61791282	M32 x 1.5	5.91	150	1.10	28	1
61791283	M40 x 1.5	6.69	170	1.10	28	1
61791284	M50 x 1.5	7.48	190	1.26	32	1

SKINMATIC® QUICK Set

Torque wrench set



Ratchet set for metric SKINTOP® plastic and brass cable glands.
Set includes one ratchet with extension, and open nuts for four sizes:
• M12 • M16 • M20 • M25

SKINTOP® QUICK Set

Part number	Width of flats mm	Pack size
61610000	15, 16, 19, 20, 25, 30	1

torque wrench

Part number	Measuring range	Pack size
61610012	2 - 10 N m	1
61610013	5 - 25 N m	1