



3602U Series

Electromagnetic Locks



3602U Electromagnetic Locks

Schlage introduces the integrators an answer to the practical needs for electromagnetic locks. These compact electromagnetic locks are easy to stock, easy to select and easy to install. Schlage 3602U with 1200 lbs of holding force.

The Variety and flexibility of Schlage 3602U family electromagnetic locks can meet your demands for high security, traffic control, or narrow line applications throughout your facility.

All models are ideal for open architecture and easily interface with electronic access control systems, automatic door operators, and fire or other hazard sensing systems for egress and emergency egress.

Benefits of using 3602U Electromagnetic Locks

- Field Selectable 12 or 24 VDC operation
- Simplified armature installation
- Variety of installation brackets available to adapt All kinds of environment
- Double magnet available with 3600U Series
- UL294 and UL10C certification
- 500,000 Times life-cycle

3602U Electromagnetic Locks

How to order 3602U

3602U

Select model

1. Select Model

3602U High security, double lock

Specifications

3602U

Holding force	1200lbs. per door leaf
Input voltage	12/24VDC field selectable
Current draw	1A@12VDC; 0.25A@24VDC.
Dimension	Lock body 536x73x40mm Armature plate 185x61x16mm Armature plate W/DSM 252x61x16mm
Weight	21.50lbs.

About Allegion

Allegion(NYSE: ALLE) is a global pioneer in seamless access, with leading brands like CISA®, Interflex®, LCN®, Schlage®, SimonsVoss® and Von Duprin®. Focusing on security around the door and adjacent areas, Allegion secures people and assets with a range of solutions for homes, businesses, schools and institutions. Allegion had \$2.7 billion in revenue in 2018, and sells products in almost 130 countries. For more, visit www.allegion.com/mea

