



# nVent CADDY Pyramid ST Fixed Strut Support – PSF10C



- Provides superior support for pipe, conduit, duct, cable tray and equipment
- Foam bottom offers low abrasion interface for better roof membrane protection
- Compatible with roof surfaces including single ply, bituminous, metal and spray foam
- Provides superior load distribution, even with varying rooftop surfaces
- Ready to use out of the box, saving installation time and labor
- Multiple sizes and load ratings offer the ability to tailor the solution to the application
- Easy to transport to the roof
- Hot-dip galvanized and UV stabilized for long lasting performance
- Supports green building requirements; thermoplastic bases are made from recycled material and can contribute to earning LEED credits



Part Number	PSF10C
Material	Polyethylene Polypropylene Steel
Finish	Hot-Dip Galvanized
Temperature	-50 to 150 °F
Static Load Safety Factor	3:1
Length 1 (L1)	10"
Length 2 (L2)	12 1/2"
Height (H)	4.8"
Width (W)	8"
Surface Area	92 in <sup>2</sup>
Unit Weight	2 lb
Static Load (F)	1,000 lb
Certifications	ITB

Part Number	PSF10C
Standard Packaging Quantity	10 pc
UPC	78285684302
EAN-13	8711893139716

Static load at 73.1 kPa (10.6 psi) roof loading. Contact project or roofing engineer for maximum allowable load on individual project roof system.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2020 nVent All rights reserved  
nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.  
All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

