

Rittal – The System.

Faster – better – everywhere.

► Air baffle plate for VX IT 482.6 mm (19") mounting angles, dynamic – DK 5302.009

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Air baffle plate for VX IT 482.6 mm (19") mounting angles, dynamic – DK 5302.009

created: 17.12.2020 on www.rittal.com/com-en



Product description

Description:	For selectively boosting the energy efficiency of a climate control system.
Benefits:	Vertical brush strip for collision-free shielding with installed rail systems on the outer mounting level.
Applications:	To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.
Material:	Sheet steel Blanking panel: Plastic, UL 94-HB, halogen-free Brush strip: Plastic, UL 94-HB
Surface finish:	Spray-finished
Colour:	RAL 9005
Assembly instruction:	The vertical trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting angles for partitioning. The horizontal trim panels with brush strips can only be mounted on the front 482.6 mm (19") mounting angles. 482.6 mm (19") mounting cut-outs integrated within the partitioning areas may optionally be sealed with the supplied blanking panels, or used to install additional components or for cable routing. Please see the product-specific scope of supply.
Supply includes:	2 vertical trim panels 2 horizontal trim panels 4 brush strips 4 cellular PU foam pieces Assembly parts 6 blanking panels, 482.6 mm (19"), 1 U

Product features

To fit: Width: = 800 mm
Height: = 2450 mm

Packs of: 1 pc(s).

Copper weight (kg per piece): 0

EAN: 4028177955240

Customs tariff number: 94039010

ETIM 7.0: EC000331

ETIM 6.0: EC000331

eCl@ss 8.0/8.1: 27189272

eCl@ss 6.0/6.1: 27182590

Product description: Air baffle plate, for VX IT 19" mounting angles, dynamic, to separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.