

Rittal – The System.

Faster – better – everywhere.

Cable duct for VX IT, TE – DK 5302.053

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Cable duct for VX IT, TE – DK 5302.053

created: 17.12.2020 on www.rittal.com/com-en



Product description

Description:	Cable duct for concealed cable routing. Convenient access to the cabling at any time via the hinged duct cover, optionally removable. The duct has cable entry options to the enclosure interior and through the rear panel of the duct. The cable retaining bars enclosed with the duct are snap-mounted onto the cable fingers of the duct with variable depth to support cable routing. Alternatively, the cable duct may also be screw-fastened. For optimum air routing, it may be combined with the brush kit for VX IT.
Benefits:	Simple assembly with tool-free quick-release fastening High packing density due to U-based cable routing Suitable for back-to-back baying Cable duct may be used as a shielding element to prevent air short-circuits within cold aisle containment Lockable cable glands, may be fitted with installation components on the 1 U mounting standard
Material:	Sheet steel Plastic to UL 94-HB
Colour:	RAL 9005
Supply includes:	Cable duct 2 covers 14 cable fingers , 6 U 10 cable retaining bars Assembly parts

Product features

To fit:	Enclosure type: VX IT Enclosure type: TS IT Width: = 800 mm Height: = 2200 mm Height: = 2200 mm
----------------	---

Units:	47 U
Packs of:	1 pc(s).
Copper weight (kg per piece):	0
EAN:	4028177958593
Customs tariff number:	39259020
ETIM 7.0:	EC000012
ETIM 6.0:	EC000012
eCl@ss 8.0/8.1:	27400703
eCl@ss 6.0/6.1:	27400703
Product description:	Cable duct, 47 U, for concealed cable routing. For enclosure width 800 mm, for enclosure height VX IT 2200 mm