

# Rittal – The System.

Faster – better – everywhere.

## **Network/server rack VX IT with glazed door, pre-configured, with 482.6 mm (19") swing frame – VX 5307.157**

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Network/server rack VX IT with glazed door, pre-configured, with 482.6 mm (19") swing frame – VX 5307.157

created: 17.12.2020 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Product description

<b>Material:</b>	Sheet steel Aluminium Plastic Glazed door: Single-pane safety glass, 3 mm
<b>Surface finish:</b>	Enclosure frame: Dipcoat-primed Interior installation: Spray-finished Rear panel and roof: Dipcoat-primed, powder-coated Front door: Aluminium, anodised/spray-finished
<b>Colour:</b>	Enclosure frame, rear panel and roof: RAL 7035 Front door: Vertical sections, silver coloured and horizontal sections, RAL 9005 Interior installation, base/plinth: RAL 9005 Handle and hinges: RAL 9005
<b>Supply includes:</b>	VX enclosure frame with doors and roof plate Glazed aluminium door at the front (180°), with comfort handle for semi-cylinder and security lock 3524 E Rear panel Roof plate, multi-piece, removable, with side cable entry in the depth and covered cut-out for fan mounting plate Base module mounted at front as infill panel Swing frame, large, with side trim panel for the installation of 482.6 mm (19") mounting components whilst utilising the full rack height, 130° Side panels, one-piece, for screw fastening Base/plinth system VX, 100 mm, vented Base/plinth corner pieces and trim panels, sides, screw-fastened Base/plinth trim panels, front and rear plus corner and baying covers supplied loose 4 levelling feet, M12, including base/plinth adaptor (supplied loose) Spacers, height 50 mm, to raise the cover plate above the fan cut-out in the roof plate, for passive cooling (supplied loose) 12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose) 25 multi-tooth screws, conductive (supplied loose)

4 combination rails for inner and outer mounting level, to fit rack depth (supplied loose)  
 10 cable shunting rings, metal, 125 x 65 mm (supplied loose)  
 IPPC pallet

<b>Note:</b>	Depending on how and where it is sited, the door opening angle may vary for selected applications
<b>Basic material:</b>	Sheet steel
<b>Product features</b>	
<b>Dimensions:</b>	Width: 800 mm Height: 2000 mm Height (enclosure with plinth): 2100 mm Depth: 800 mm
<b>Free mounting space to the 482.6 mm (19") level, front/rear:</b>	150 cm / 570 cm
<b>Load capacity:</b>	3500 N
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	150 kg
<b>EAN:</b>	4028177944985
<b>Customs tariff number:</b>	94032080
<b>ETIM 7.0:</b>	EC002499
<b>ETIM 6.0:</b>	EC002499
<b>eCl@ss 8.0/8.1:</b>	27180207
<b>eCl@ss 6.0/6.1:</b>	27180207
<b>Product description:</b>	VX IT, swing frame, glazed door, WHD: 800 x 2100 x 800 mm, 40 U, pre-configured
<b>Approvals</b>	
<b>Approvals:</b>	UL + C-UL
<b>Declarations:</b>	Declaration of conformity