

Rittal – The System.

Faster – better – everywhere.

VX SE free-standing enclosure system – SE 5822.600

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX SE free-standing enclosure system – SE 5822.600

created: 17.12.2020 on www.rittal.com/com-en



Product description

Material:	Enclosure: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Gland plates: Sheet steel, 1.5 mm Mounting plate: Sheet steel, 3.0 mm
Surface finish:	Enclosure, door and rear panel: dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and gland plates: Zinc-plated
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55
Protection category NEMA:	NEMA 12
Supply includes:	Enclosure, solid top and sides Door(s) R/h door hinge with single-door enclosures, may be swapped to opposite side Mounting plate Gland plates Rear panel, detachable Lock: 3 mm double-bit 2 punched rails 18 x 39 mm Rear panel, one-piece

Product features

Dimensions:	Width: 800 mm Height: 1800 mm Depth: 300 mm
--------------------	---

Mounting plate:	Width: 699 mm Height: 1696 mm
Number of doors:	1
Packs of:	1 pc(s).
Weight/pack:	118 kg
EAN:	4028177959262
Customs tariff number:	94032080
ETIM 7.0:	EC000261
ETIM 6.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Product description:	VX SE Free-standing enclosure system, WHD: 800x1800x300 mm, Sheet Steel, with mounting plate, single door at the front
Approvals	
Approvals:	UL + C-UL
Certificates:	Protection category
Declarations:	Declaration of conformity