

# Rittal – The System.

Faster – better – everywhere.

## ▶ VX SE free-standing enclosure system IP 66/NEMA 4 – SE 5831.680

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX SE free-standing enclosure system IP 66/NEMA 4 – SE 5831.680

created: 17.12.2020 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Product description

<b>Material:</b>	Enclosure: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Base: sheet steel, 1.5 mm Mounting plate: Sheet steel, 3.0 mm
<b>Surface finish:</b>	Enclosure, door and rear panel: dipcoat-primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated Base: Dipcoat-primed and powder-coated, textured paint
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	IP 66
<b>Protection category NEMA:</b>	NEMA 4
<b>Supply includes:</b>	Enclosure, solid top and sides Door(s) Door hinged on the right, may be swapped to the left Mounting plate Base, solid Rear panel, detachable Lock: 3 mm double-bit 2 punched rails 18 x 39 mm

## Product features

<b>Dimensions:</b>	Width: 800 mm Height: 1800 mm Depth: 400 mm
--------------------	---

<b>Mounting plate:</b>	Width: 699 mm Height: 1696 mm
<b>Number of doors:</b>	1
<b>Packs of:</b>	1 pc(s).
<b>EAN:</b>	4028177959309
<b>Customs tariff number:</b>	94032080
<b>ETIM 7.0:</b>	EC000261
<b>ETIM 6.0:</b>	EC000261
<b>eCl@ss 8.0/8.1:</b>	27180101
<b>eCl@ss 6.0/6.1:</b>	27180101
<b>Product description:</b>	VX SE Free-standing enclosure system, WHD: 800x1800x400 mm, Sheet steel, with mounting plate, single door at the front
<b>Approvals</b>	
<b>Approvals:</b>	UL + C-UL
<b>Declarations:</b>	Declaration of conformity