

Rittal – The System.

Faster – better – everywhere.

PSM Zero-U-Space – DK 7859.080

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PSM Zero-U-Space – DK 7859.080

created: 17.12.2020 on www.rittal.com/com-en



Product description

Description:	Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.
Material:	Aluminium section, natural anodised
Assembly instruction:	Various connection cables, also for single-phase connection
Protection category IP to IEC 60 529:	IP 20

Product features

Module slots (max.):	6
To fit:	Height: > 2000 mm
Dimensions:	Length: 1695 mm
Infeeds:	Qty.: 2 Phases per infeed: 3~
Ambient conditions:	Operating temperature: +5 °C...+45 °C Ambient humidity (non-condensing): 10 % - 90 %
Type of electrical connection:	Wago jack X-COM
Rated current (max.):	16 A
Packs of:	1 pc(s).

Copper weight (kg per piece):	0
EAN:	4028177956650
Customs tariff number:	85369001
ETIM 7.0:	EC000215
ETIM 6.0:	EC000215
eCl@ss 8.0/8.1:	27371306
eCl@ss 6.0/6.1:	27371306
Product description:	DK modular PDU, PSM busbar, modular power distribution for vertical installation, in the Zero-U-Space for 800 mm wide IT racks, 3~, 16 A, length 1695 mm, module slots: 6, infeeds: 2, connection: WAGO socket, x -COM, for enclosure height 2000 mm, aluminium section, natural anodised