3399 Fox & Hound™ Premium Tone and Probe Kit

Lightweight and easy to use wire tracing kit

Features:

- · Constructed with high quality materials
- · Portable design allows you to trace wires whenever needed
- · Find non-energized wires in walls, ceilings, and floors
- · Three methods of contactivity; RJ11, RJ45 and alligator clips

Fox 2 Features:

- · Battery operated handheld multi-function Toner
- · Generates multiple tones (Pulse or Warble)
- Performs basic telephone line tests (loop mA, line polarity, and ringing voltage)
- · Provides a visual and audible continuity test
- · Integrates True Trace and TripLatch tests
 - "True Trace" allows for definite ID of target wire pair
 - · Cordless Phone Interface for hands-free "True Trace"
 - "Trip-Latch" a unique latch testing technique using "True Trace for testing Alarm Sensors
- · Overload protection up to 120 VAC.

Hound 3 Features:

- Battery operated handheld lightweight Probe
- Thumbwheel Sensitivity control
- · Signal Strength indicator LED
- Built-in LED headlights to illuminate dark areas and reduce fluorescent light noise
- · Bandpass filter to suppresses unwanted frequencies
- · Earphone jack for noisy or quiet work areas
- This kit includes Fox 2, Hound 3, RJ-11 to RJ-45 adapter, plastic duck bill, metal duck bill, headphones, and a sturdy weatherproof carry case. 2 x 9V batteries not included
- · 1 year warranty







"Line to ground" testing using Alligator clips

Ordering Information:

3399

Fox & Hound™ Premium Tone and Probe Kit











